


# 35 Electronics Pliers



DIN ISO 9655

- ▶ precision pliers for ultra fine assembly work, e. g. in electronics and fine mechanics
- ▶ for gripping, holding and bending
- ▶ precision box joint
- ▶ smooth ground gripping surfaces
- ▶ edges carefully deburred
- ▶ low-friction double spring for gentle and even opening
- ▶ the polish or mirror polish (only finish 2) together with a fine film of oil offer the best possible rust protection - no circuit faults caused by peeling chrome from plated tools
- ▶ special tool steel, oil-hardened and tempered

**special**

**KNIPEX**

In the design of KNIPEX Electronics Pliers for gripping and cutting ergonomic criteria have been given particular attention. The result is a comfortable and user friendly adaption of the plier to the human hand.

35 12 115



Style 1: flat, wide jaws



35 22 115



Style 2: half-round jaws



35 32 115



Style 3: round, pointed jaws



35 52 145



Style 5: long, trapezoidal jaws



35 72 145



Style 7: round, long jaws



35 42 115



Style 4: 45° bent, half-round jaws



35 62 145



Style 6: half-round, long jaws





35 82 145



Style 8: 45° bent, half-round, long jaws



00 20 16



| Article-No. | EAN-Code | Style | Head            | Handles                                | Dimensions |      |     |     |     | g   |
|-------------|----------|-------|-----------------|--|------------|------|-----|-----|-----|-----|
|             |          |       |                 |  | B          | A    | D   | E   | F   |     |
| 35 11 115   | 016694   | 1     | polished        | plastic coated                         | 22.5       | 9.5  | 6.5 | 2.0 | 4.0 | 60  |
| 35 12 115   | 035107   | 1     | mirror polished | with two-colour dual component handles | 22.5       | 9.5  | 6.5 | 2.0 | 4.0 | 75  |
| 35 21 115   | 016724   | 2     | polished        | plastic coated                         | 22.5       | 9.5  | 6.5 | 2.0 | 1.5 | 55  |
| 35 22 115   | 035114   | 2     | mirror polished | with two-colour dual component handles | 22.5       | 9.5  | 6.5 | 2.0 | 1.5 | 70  |
| 35 31 115   | 016762   | 3     | polished        | plastic coated                         | 22.5       | 9.5  | 6.5 | 2.0 | 1.0 | 50  |
| 35 32 115   | 035121   | 3     | mirror polished | with two-colour dual component handles | 22.5       | 9.5  | 6.5 | 2.0 | 1.0 | 60  |
| 35 42 115   | 040736   | 4     | mirror polished | with two-colour dual component handles | 22.5       | 9.5  | 6.5 | 2.0 | 1.5 | 75  |
| 35 52 145   | 039389   | 5     | mirror polished | with two-colour dual component handles | 40.0       | 12.0 | 7.5 | 1.5 | 4.0 | 105 |
| 35 62 145   | 039556   | 6     | mirror polished | with two-colour dual component handles | 40.0       | 12.0 | 7.5 | 2.5 | 1.5 | 95  |
| 35 72 145   | 043607   | 7     | mirror polished | with two-colour dual component handles | 40.0       | 12.0 | 7.5 | 2.5 | 1.3 | 90  |
| 35 82 145   | 039396   | 8     | mirror polished | with two-colour dual component handles | 35.0       | 12.0 | 7.5 | 2.5 | 1.0 | 95  |