

# Section 8

## Plugs, Bases & Sockets



## Plug tops



Pack	Cat No.	Colour codes:BL (Black), CL (Clear), GY (Grey), WE (White) <b>Large finger-grip, rigid, impact-resistant moulding, 250V a.c.</b>
10	90	10A plug top, 3 pin flat (BL,WE)
10	90/15	15A plug top, 3 pin flat (BL, GY, WE)
10	90/20	20A plug top, 3 pin flat (GY,WE)
10	90/25	25A plug top, 3 pin, L-shaped earth, flat active and neutral (WE)
10	90R	10A plug top, 3 pin, round earth, flat active and neutral (WE)
10	94	10A plug top, 4 pin plug for use with Cat. No 33 and 34 series. Available in white only (WE)



Pack	Cat No.	<b>Low profile side entry with 45° cord entry and screwed clamp terminals, 250V a.c.</b>
10	106/1	10A plug top, 3 pin flat. (BL, GY, WE)
10	106/2	10A plug top, 3 pin flat, accepts 15A heavy duty flexible cord. (WE)
10	106/3	15A plug top, 3 pin flat (BL, WE)
10	106/4	20A plug top, 3 pin flat (BL, WE, GY)
10	106/5	25A plug top, 3 pin, L-shaped earth, flat active & neutral (WE)
10	106/6	10A plug top, 3 pin, round earth, flat active & neutral (BL, WE, GY)
10	106/7	10A plug top, 3 pin, flat earth, round active & neutral (BL, WE, GY)
10	106/8	32A plug top, 3 pin, U-shaped earth, flat active & neutral (WE)



Pack	Cat No.	<b>Flexible PVC cover with cord locking nut, and screwed clamp terminals, 250V a.c.</b>
10	100L	10A plug top, 3 pin flat, locking nut, 8mm entry hole (BL, CL, GY, WE)
10	100LHD	10A plug top, 3 pin flat, 10mm entry hole for 15A heavy duty cord (CL, GY)
10	100/8	10A plug top, 3 pin flat, figure 8 wire (BL, WE)
10	100R	10A plug top, 3 pin, round earth, flat active & neutral (BL, CL, GY, WE)
10	100/2R	10A plug top, 3 pin, flat earth, round active & neutral (CL, GY, WE)
10	100L15	15A plug top, 3 pin flat (CL, GY, WE)

## Plug bases



Pack	Cat No.	<b>Plug bases, surface, 250V a.c.</b> Mounting centres: 50mm. Size 65mm dia x 48mm high. Standard colour is clear.
10	37	10A plug base, 3 pin flat, includes Cat. No. 37B snap-on base plate.
10	37/15	15A plug base, 3 pin flat
10	37R	10A plug base, 3 pin, round earth, flat active & neutral
10	37B	Snap-on base plate for Cat. No. 37 range. Also fits Cat. No. 366, 80 & 33



Pack	Cat No.	<b>3 pin plug surface bases, low profile, 250V a.c.</b>
10	35	10A surface base, 3 pin flat (BR, BL, WE)



Pack	Cat No.	<b>Plug bases for panel or flush mounting, 250V a.c.</b> Supplied as base mechanism plus front plate. Size: 38mm dia x 25mm deep. Minimum order quantities may apply - please check prior to ordering
10	38	10A plug base, 3 pin flat, suits panel thickness of 2.5mm (BL, MG, WE)
10	38A0	10A plug base, 3 pin flat, suits panel thickness of 1.0mm (BL, WE)
10	38A1	10A plug base, 3 pin flat, suits panel thickness of 1.2mm (WE)
10	38A2	10A plug base, 3 pin flat, suits panel thickness of 1.5mm (WE)
10	38A3	10A plug base, 3 pin flat, suits panel thickness of 1.6mm (BL, WE)
10	38A4	10A plug base, 3 pin flat, suits panel thickness of 2.0mm (WE)
10	38A5	10A plug base, 3 pin flat, suits panel thickness of 2.2mm (WE)
10	38R	10A plug base, 3 pin, round earth, flat active & neutral, suits panel thickness of 2.5mm (WE)
10	38/2R	10A plug base, 3 pin, flat earth, round active & neutral, suits panel thickness of 2.5mm (WE)
10	38/15	15A plug base, 3 pin flat, suits panel thickness of 2.5mm (BL, WE)
10	38/20	20A plug base, 3 pin flat, suits panel thickness of 2.5mm (WE)
10	38/25	25A plug base, 2 pin flat with L earth pin, suits panel thickness of 2.5mm (WE)



Pack	Cat No.	<b>Plug base and plate assemblies</b> Mounting centres: 95mm. Suits standard mounting accessories. Can be mounted horizontally or vertically. Size: 114 x 70mm.
10	38/1	10A, Cat. No. 38 plug base on plate (BL, RED, WE)
10	38/115	15A, Cat. No. 38/15 plug base on plate (WE)
10	38/1R	10A, Cat. No. 38R plug base on plate (WE)
10	38/120	20A, Cat. No. 38/20 plug base on plate (WE)
10	38/12R	10A, Cat. No. 38/2R plug base on plate (WE)
1	38/1PL	Plate only suit 38 series (WE)



Pack	Cat No.	<b>4 pin plug surface bases, 250V a.c.</b>
10	33	10A 4 pin plug base with looping terminal. 50mm mounting centres. 69 x 69 x 46mm. (WE)
10	33B	Snap-on base plate for Cat. No. 33 range. 58mm mounting centres. 114 x 70mm. (CL)
10	34B	Snap-on base plate for Cat. No. 34 range. 91mm mounting centres. 150 x 70mm (CL)

## Extension sockets



Pack	Cat No.	Flexible PVC cover with safety skirt, cord locking nut and screwed clamp terminals, 240V a.c. Colour codes: BL (Black), CL (Clear), GY (Grey), WE (White).
10	7P	10A extension socket, 3 pin flat, 8mm entry hole (BL, CL, GY, WE)
10	7P15	10A extension socket, 3 pin flat, 10mm entry hole (CL, GY, WE)



Pack	Cat No.	Elbow plug socket
10	39	10A elbow plug socket

## Ceiling roses



Pack	Cat No.	Latching cover ceiling roses, 240V a.c. Colour codes, BL (Black), WE (White).
10	80	(WE) Ceiling rose, 4 way connection. Easily wired with connectors supplied. 68mm dia x 44mm high.
10	84	<b>Screw-on cover ceiling roses, 240V a.c.</b> Size: 65mm dia x 37mm high. Ceiling rose 10A, 4 plate x 2 post per plate (BL, BR, WE)
10	78	<b>Large screw-on cover type, 240V a.c.</b> Size: 92mm dia x 36mm high. Ceiling rose 10A, 4 plate x 2 posts per plate (WE)

## Battenholders



Pack	Cat No.	240V. a.c. To suit B22 bayonet cap lamps. Supplied with long skirt, (Cat. No. 333SK). <b>Battenholder, 4 terminals</b>
10	360	Adjustable angle battenholder, 4 large terminals. 64mm dia base. 50mm mounting centres. (WE)
5	360/W1	Adjustable angle battenholder, IP23. 4 terminals. Integral anchor plugs. 50mm mounting centres. (WE)
10	366	Battenholder, 4 terminals, standard 68mm dia base. 50mm mounting centres. (WE)
10	366Y	Battenholder, 4 terminals, integral fix-fast anchor plugs, standard 68mm dia base. 50mm mounting centres. (WE)
10	366LY	Battenholder, 4 terminals, separate fix-fast anchor plugs, standard 68mm dia base. 50mm mounting centres. (WE)
10	368	Battenholder, 4 terminals, 90mm dia base. 50mm mounting centres. (WE)
10	368/1	Battenholder, 4 terminals, 90mm dia base. 70mm mounting centres. (WE)

## Lampholders



Pack	Cat No.	BC cord grip, 240V. Colour codes: BL (Black), WE (White)
10	333	Lampholder, cord grip, supplied with long skirt, (Cat. No. 333SK) (BL, WE)



Pack	Cat No.	<b>Tapered cap - top cable entry</b> Supplied with long skirt, (Cat. No. 333SK)
10	359/10	Lampholder with 10 mm thread (1.0 mm pitch) (BR, BL, WE)



Pack	Cat No.	<b>Tapered cap - side cable entry</b> Supplied with long skirt, (Cat. No. 333SK). Threaded hole is blind for insulation from terminal area.
10	359A10	Lampholder with 10mm thread (1.0mm pitch) (WE)



Pack	Cat No.	<b>Switched lampholders - tapered cap - top cable entry</b> 240V a.c. Double pole push bar switch with red dot indication. Supplied with long skirt, (Cat. No. 333SK).
10	310	Switched lampholder with 1/2 inch brass thread with nipple (WE)
10	310/10	Switched lampholder with 10mm thread (1.0mm pitch) (WE)



Pack	Cat No.	<b>Festoon lampholders</b> Mounting centres: 50mm. 3A, 240V a.c.. BC with side entry cable, wire piercing connections. Overall height 65mm.
10	303/1F	Lampholder with fanged screw-on cap & long skirt, (Cat. No. 333SK) (BL)
10	WS303/1R	Lampholder with round screw-on cap & rubber skirt for weatherproofing (BL)
10	WS303/1F	Lampholder with fanged screw-on cap & rubber skirt for weatherproofing (BL)

## Lampholder accessories



Pack	Cat No.	<b>Lampholder skirts</b>
10	A1801	Lampholder skirt (short), 24mm (WE)
10	A5625	Lampholder skirt (medium), 30mm (WE)
10	333SK	Lampholder skirt (long), 37 mm (WE)