


**PV-YC 4/ 1-0,12-SO2 (-/++)**

Order No.: 1795019

<http://eshop.phoenixcontact.co.uk/phoenix/treeViewClick.do?UID=1795019>

Photovoltaic Y distributor, Nominal current: 40 A, Color: black,  
Assembled with SUNCLIX - 1 x male (minus) - 2 x female (plus);  
length of single cable 0.12 m, varying number of nodes and customer-  
specific cable lengths are available on request.

**Commercial data**

EAN	 4 046356 632263
Pack	10
Customs tariff	85446010
Country of Origin	DE

**Product notes**WEEE/RoHS-compliant since:  
03/11/2010

Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation at <http://www.download.phoenixcontact.com>. The General Terms and Conditions of Use apply to Internet downloads.


**Technical data****Technical data**

Standards/regulations	DIN EN 50521 (in accordance with)
Rated voltage (III/2)	1100 V
Rated surge voltage (III/2)	12 kV
Rated current	40 A (observe derating)

Nominal cross section	4 mm <sup>2</sup>
Protection class	II
Degree of protection	IP65/IP68
Inflammability class according to UL 94	V0
Ambient temperature (operation)	-40 °C ... 90 °C

## Drawings

### Dimensioned drawing



**Address**

PHOENIX CONTACT Ltd  
Halesfield 13  
Telford / Shropshire / TF7 4PG,England  
Phone 01952 681 700  
Fax 01952 681 799  
<http://www.phoenixcontact.co.uk>



Phoenix Contact Ltd.  
Technical modifications reserved;