

# Rail Mounted Terminal Blocks

## 9503310000

When good enough just isn't good enough

**Weidmüller** 

KDKS 1 (TS35)

[Email to a Friend](#)

[View Catalog Page](#)

[Sales Information](#)

[Back to StepSearch](#)

[Catalog Home](#)



Representative Phot

### Technical Information

Clamping Type	Screw Clamp
Series	W Series
Rail Type	TS 35
Function	Circuit Protection Disconnect
Configuration	Fuse and Feed Through Lever and Feed Through
Wire Size	#22...12 AWG
Current	10 A upper level, 20 A lower level
Voltage	300 V
Color/Material	Beige PA

### Technical Data

	UL	CSA	VDE
Rated Voltage	300 V	300 V	500 V
Rated Current	10 A 20 A	10 A 25 A	
Wire Size	#22...12 AWG	#22...12 AWG	4 mm <sup>2</sup>

### Additional Data

Width/Length/Height mm (in.)	8/73.5/55.7 (.31"/2.89"/2.19")
Insulation Stripping Length mm (in.)	9 (.35")
Torque Nm (lb. in)	0.6 (5.5)
Clamping Screw	M 3
Flammability Class	UL 94 (V2)

### Suggested Accessories

[DIN-rail](#)

[End bracket](#)

[End plate/partition \(AP/TW\)](#)

[Ferrules](#)

[Fuses](#)

[Marking pens](#)

[Marking tags \(DEK\)](#)

[Mounting brackets](#)

[Tools](#)

---

**Product Liability** The above information describes our products. It does not constitute guaranteed properties and is not intended to a the suitability of a product for a particular application. Regrettably, omissions and exceptions cannot be completely ruled out. Techni data are always specified by their average values. Exact data and the tolerances which apply to our processes can be requested from

**Weidmüller - North America**  
United States 001 (800) 849-9343  
Canada 001 (800) 268-4080

or

**Weidmüller - Germany**  
Telephone operator 0049 (-5252) 960-0