



BU-00000- *
Part # color

* 0 - Black 5 - Green
2 - Red 6 - Blue
4 - Yellow 9 - White

CLIPS & INSULATORS



Enlarge

BU-24APN Heavy Duty 25 - Amp Clip (unmarked)
BU-24APS Heavy Duty 25 - Amp Clip (marked positive)

- Steel
- Crimp or screw connection
- Rugged teeth on one jaw
- Jaw opens 3/4" (19mm) max
- For battery operated equipment, chargers, trouble lights
- [Product Data Sheet](#)
- [Send us your questions about this product](#)

Automotive Clip - 40 Amp
BU-25 (Steel)
BU-25C (Solid Copper)

- Teeth mesh on all 3 sides
- Jaw opening: 3/4" (19mm) max
- Crimp or screw connection
- Federal Spec.: Type PC-4 W-C-440B (BU-25C)
- [Product Data Sheet](#)
- [Send us your questions about this product](#)



Enlarge

BU-26-* Insulator for Heavy Duty and Automotive Clips



Enlarge

- Vinyl insulator
- Available in black, red, yellow, green, blue, white
- [Product Data Sheet](#)
- [Send us your questions about this product](#)

Heavy Duty Clip for Battery & Test Work:

BU-21APN Unmarked, Steel - 50 Amp
BU-21APS Marked positive, Steel - 50 Amp
BU-21CPN Unmarked, Solid Copper - 100 Amp
BU-21CPS Marked positive, Solid Copper - 100 Amp

- Copper shunt eliminates spring overheat
- BU-21CPN/CPS, removable copper lug - attach to cable
- Crimp, screw, lug connection
- Federal Spec.: Type PCL-1 W-C-440B (BU-21CPN)
- [Product Data Sheet](#)
- [Send us your questions about this product](#)



Enlarge

[Insulated BNCs](#)|[Test Leads](#)|[Insulated Test Accessories](#)
[Accessories & Probes](#)|[Kits](#)|[Cross Reference](#)

©2003 Mueller Electric Company. All rights reserved.
Problems with the site should be reported to the [webmaster](#).