



BU-00000- \*  
Part # color

\* 0 - Black 5 - Green  
2 - Red 6 - Blue  
4 - Yellow 9 - White

**CLIPS & INSULATORS**

### BU-30BL Miniature-Alligator with Barrel 5 Amp



Enlarge

- Full meshing teeth
- Rolled barrel tail section
- Steel
- Solder or crimp connection
- 3/16" (4.8mm) maximum jaw opening
- [Product Data Sheet](#)
- [Send us your questions about this product](#)

### BU-30TBO Miniature Alligator with Threaded Barrel - 5 Amp

- Steel with threaded steel barrel
- Connects to any 6-32 threaded male test prod
- [Product Data Sheet](#)
- [Send us your questions about this product](#)



Enlarge



Enlarge

### BU-31 Insulator for BU-30BL or BU-30TBO

- Tough flexible vinyl
- Available in black, red, yellow, green, blue and white
- [Product Data Sheet](#)
- [Send us your questions about this product](#)

### Alligator Clip with Barrel 10 Amp:

**BU-60 (Steel)**

**BU-60C (Solid Copper)**

**BU-60X (Stainless Steel)**

- Standard clip with barrel for a banana plug
- Solder or crimp connection
- 5/16" (7.9mm) max. jaw opening
- Nose width 0.13"
- Stainless steel clip, body, rivet and spring
- [Product Data Sheet](#)
- [Send us your questions about this product](#)



Enlarge

[Insulated BNCs](#)|[Test Leads](#)|[Insulated Test Accessories](#)  
[Accessories & Probes](#)|[Kits](#)|[Cross Reference](#)

©2003 Mueller Electric Company. All rights reserved.  
Problems with the site should be reported to the [webmaster](#).