

H0,14/12 GR SV**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16


D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-2083

www.weidmueller.com



- Weidmüller colour code
- in multipack bag (5 x 100 pcs.)

General ordering data

Order No.	9028240000
Type	H0,14/12 GR SV
Version	Wire end ferrule, 0.14 mm ² , 8 mm, Colour code: Weidmüller, Grey
GTIN (EAN)	4008190902001
Qty.	500 pc(s).

H0,14/12 GR SV

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-2083

www.weidmueller.com

Technical data

Dimensions

Length 12 mm

Product data

Conductor cross-section	0.14 mm ²	Contact surface length (L2)	8 mm
Contact surface diameter (D1)	0.6 mm	Collar diameter (D2)	1.5 mm
Metal sleeve thickness (S1)	0.15 mm	Plastic collar thickness (S2)	0.25 mm

Classifications

ETIM 2.0	EC000005	ETIM 3.0	EC000005
ETIM 4.0	EC000005	UNSPSC	31-16-31-02
eClass 4.1	27-06-07-01	eClass 5.1	27-40-02-01
eClass 6.0	27-40-02-01	eClass 7.0	27400201

Product information

Description of article Wire end ferrule with plastic collar, grey

Approvals

Approvals

