




TYPE - CFS90IP68



Contact your local
Sales Representative
[Click Here for
Printable Version](#)

				NPT	Threaded	Fittings			
Cat #	US Trade Size	MM	NW	Thread Size	Unit Pack	Part #	Standard Carton	Part #	List Price Per 100 Pcs.
CFS-140A	1/4"	10	7	PG-7	1	90821	-	-	\$977.00
CFS-516A	5/16"	12	10	PG-9	1	90823	-	-	\$1,010.00
CFS-20	3/8"	16	12	1/2" NPT	25	90901	100	90902	\$941.00
CFS-21	1/2"	20	17	1/2" NPT	25	90911	100	90912	\$987.00
CFS-22	3/4"	25	23	3/4" NPT	10	90921	50	90922	\$1,316.00
CFS-23	1"	32	29	1" NPT	10	90931	30	90932	\$1,474.00
CFS-24	1-1/4"	40	36	1-1/4" NPT	5	90941	20	90942	\$2,695.00
CFS-25	1-1/2"	50	48	1-1/2" NPT	2	90951	10	90952	\$2,920.00



TYPE - CFS90IP68

IP 68 is the equivalent to NEMA 6 and can withstand water from entering during submersion

Plastic Used: NYLON [See the Chemical Resistance Guide](#)

High Mech. Strength	Listed For Direct Burial	Halogen Free	Low Fire Hazard	Accepts Standard Liquidtight Fittings	Self Extinguish	EMI/RFI Shielding	Oil Resistance	Acid Resistance