

Round Hole Panel Jacks

Type RSJ Standard Size - Type RMJ Miniature Size


FRONT MOUNT HARDWARE INCLUDED!

28.7 mm (1.13")
Square Bezel



12.7 mm (0.50")
14 NPSL Threads

Rear View



28.7 mm (1.13)
Dia. Bezel




22.4 mm (0.88")
Dia. Cutout

FEATURES

- ✓ Standard Accepts All Industry Standard Size Connectors
- ✓ Miniature Accepts All Industry Miniature Size Connectors
- ✓ Mounts in Round or "D" Punch Holes
- ✓ Square or Round Bezel to Match Your Panel Components
- ✓ Heavy Duty Glass-Filled Nylon Rated to 220°C (425°F)
- ✓ Polarity Keyed
- ✓ Color-Coded
- ✓ No Filing Required

EASY INSTALLATION

No special tooling is required for installation. Just drill or punch a round hole in your panel and tighten the supplied nut. Ideal for single-circuit applications where the connector must blend with existing instrumentation. Thermocouple circuits can be added to existing panels with only minimal interruption of operations. A choice of either square or round face is available to match the design lines of your installation. Thermocouple grade alloys used to form the contacts preserve the accuracy of the circuit even in changing ambient temperatures.





For RHP, CP and RHS Series panel punches and saws

Accepts Standard Size Connectors

To Order (Specify Model No.)

| Alloy Code | Color | Model Number | |
|------------|--------|--------------|------------|
| | | Square Face | Round Face |
| K | Yellow | RSJ-K-S | RSJ-K-R |
| T | Blue | RSJ-T-S | RSJ-T-R |
| J | Black | RSJ-J-S | RSJ-J-R |
| E | Purple | RSJ-E-S | RSJ-E-R |
| R/S | Green | RSJ-R/S-S | RSJ-R/S-R |
| U | White | RSJ-U-S | RSJ-U-R |



Accepts Miniature Size Connectors

To Order (Specify Model No.)

| Alloy Code | Color | Model Number | |
|------------|--------|--------------|------------|
| | | Square Face | Round Face |
| K | Yellow | RMJ-K-S | RMJ-K-R |
| T | Blue | RMJ-T-S | RMJ-T-R |
| J | Black | RMJ-J-S | RMJ-J-R |
| E | Purple | RMJ-E-S | RMJ-E-R |
| R/S | Green | RMJ-R/S-S | RMJ-R/S-R |
| U | White | RMJ-U-S | RMJ-U-R |

| Part Number | Description |
|-------------|---|
| RSJ-K-S | Standard size round hole and square face panel jack with type K calibration |
| RSJ-J-S | Standard size round hole and square face panel jack with type J calibration |
| RSJ-U-S | Standard size round hole and square face panel jack with type U calibration |
| RSJ-T-R | Standard size round hole and round face panel jack with type T calibration |
| RSJ-E-R | Standard size round hole and round face panel jack with type E calibration |
| RMJ-K-S | Miniature size round hole and square face panel jack with type K calibration |
| RMJ-J-S | Miniature size round hole and square face panel jack with type J calibration |
| RMJ-U-S | Miniature size round hole and square face panel jack with Uncompensated or type B calibration |
| RMJ-K-R | Miniature size round hole and round face panel jack with type K calibration |
| RMJ-J-R | Miniature size round hole and round face panel jack with |

| | |
|------------|---|
| RMJ-E-R | type J calibration Miniature size round hole and round face panel jack with type E calibration |
| MPJ-CAP-12 | Extra dust caps in pkg of 12. Other package sizes available |
| MH-RSJ-5 | Extra standard size mounting nuts, pkg of 5. Other package sizes available. |
| MH-RMJ-5 | Extra miniature size mounting nuts, pkg of 5. Other package sizes available. |

Part Number Builder

(1)

-

(2)

-

(3)

Option Descriptions

(1) Panel Jack Type

Select

RSJ for Standard size round hole

RMJ for Miniature size round hole

(2) Thermocouple Calibrator

Select

K for Type K

T for Type T

J for Type J

E for Type E

R/S for Type R/S

U for Uncompensated or Type B

(3) Face Type

Select

S for Square

R for Round