



by Schneider Electric

List Price \$39.00 USD

Availability **Stock Item: This item is normally stocked in our distribution facility.**

### Technical Characteristics

Approvals	UL Listed (with 8501NR socket) - UL Recognized Component - CSA Certified - CE Marked
Coil Voltage	24Vdc
Ampere Rating (Resistive)	12A
Application	Designed for multipole switching applications at 240 volts or lower
RoHS Compliant	Yes
Contact Material	Silver Tin Oxide
Mounting Type	Socket
Snapmount Socket	8501NR51 or 8501NR52
Manual Operator	No
Type of Pins	Tubular Terminals
Horsepower Rating	1/3HP@120Vac - 1/2HP@240Vac
Pilot Light	No
Contact Arrangement	DPDT
Operating Times	Pick-Up: 18ms - Drop-Out: 7ms
Operating Temperature Range	-40°F to 158°F
Relay Type	Standard
Type	K

### Shipping and Ordering

Category	21141 - Relays, General Purpose, Plug-In, Tubular Terminals, Type KP
Discount Schedule	CP2
GTIN	00785901480662
Package Quantity	1
Weight	0.2 lbs.
Availability Code	Stock Item: This item is normally stocked in our distribution facility.
Returnability	Y
Country of Origin	CN

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.