
Item no.: 264-321
Product description: 2-conductor centre terminal block



Produkt kann von Bild abweichen / product may differ

Packing unit 100 pieces

RoHS compliant

Product group	9 (Std Chassis Mt Blocks)
Cross section [mm ²]	0.08 - 2.5 mm ²
Cross section [AWG]	28 - 12 AWG
Connection method	CAGE CLAMP®CONNECTION
Measured voltage EN	800 V
Measured shock voltage	8 kV
Pollution degree	3
Current intensity EN	24 A
Weight	3.85 g
Color	grey
Wiring type	Front-entry
No. of connection Points	2
No. of potentials	1
Height	22 mm
Height	0.867 in
Width	6 mm
Width	0.236 in
Depth	32 mm
Depth	1.26 in

Strip length from
Strip length to
Strip length

8 mm
9 mm
0.33 in



Item number	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
264-321	ABS	04-HG476174/1-PDA	800	24	2,5
264-321	BV	07436/C0			0,08-2,5
264-321	CCA	NL6511	800	24	2,5
264-321	CSA	18677-23	600	20	26-12
264-321	DNV	E-9215	800	24	2,5
264-321	GL	17295-00HH	800	24	2,5
264-321	KEMA	2110272.04	800	24	2,5
264-321	KR	HMB05880-EL002	800	24	2,5
264-321	LR	92/20242(E5)	800	24	2,5
264-321	RMR	11130002	800	24	2,5
264-321	UR	E45172	300	20	28-12

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected