
Item no.: 279-681
Product description: 3-conductor through terminal block



Produkt kann von Bild abweichen / product may differ

Packing unit 100 pieces

RoHS compliant

Product group	1 (Rail Mounted Terminal Blocks)
Cross section [mm ²]	0.08 - 1.5 mm ²
Cross section [AWG]	28 - 16 AWG
Connection method	CAGE CLAMP®CONNECTION
Measured voltage EN	800 V
Measured shock voltage	8 kV
Pollution degree	3
Current intensity EN	18 A
Weight	5.198 g
Color	grey
Wiring type	Front-entry
No. of connection Points	3
No. of potentials	1
Height	27 mm
Height	1.06 in
Width	4 mm
Width	0.157 in
Depth	62.5 mm
Depth	2.46 in

Strip length from	8 mm
Strip length to	9 mm
Strip length	0.33 in
Mounting	TS 35



Item number	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
279-681	ABS	05-HG476175/3-PDA	800	18	1,5
279-681	BV	07436/Co	800	18	1,5
279-681	CCA	NL6098	800	18	1,5
279-681	CSA	154112-1327715	600	10	28-16
279-681	DNV	E-10423	800	18	1,5
279-681	GL	17295-00HH	800	18	1,5
279-681	KEMA	2105357.01	800	18	1,5
279-681	KR	HMB05880-EL001	800	19,5	1,5
279-681	LR	91/20112(E6)	800	18	1,5
279-681	PRS	TE/1718/880590/08	800	18	1,5
279-681	RMR	11130002	800	18	1,5
279-681	UR	E45172	600	10	28-16

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected