
Item no.: 769-176
Product description: 1-Conductor / 1-pin receptacle terminal block according to en 60715



Produkt kann von Bild abweichen / product may differ

Packing unit 100 pieces

RoHS compliant

Product group	18 (X-COM-SYSTEM)
Cross section [mm ²]	0.08 - 4 mm ²
Cross section [AWG]	28 - 12 AWG
Measured voltage EN	500 V
Measured shock voltage	6 kV
Pollution degree	3
Current intensity EN	32 A
Weight	5.453 g
Color	grey
Wiring type	Front-entry
No. of connection Points	2
No. of potentials	1
Height	28.5 mm
Height	1.12 in
Width	5 mm
Width	0.197 in
Depth	52.5 mm
Depth	2.07 in
Strip length from	8 mm

Strip length to
Strip length
Mounting

9 mm
0.33 in
TS 35



Item number	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
769-176	ABS	05-HG476175/3-PDA	500	16	4
769-176	CSA	154112-1101144	300	20	28-12
769-176	LR	91/20112(E6)	500	16	4
769-176	RMR	11130002	500	16	4
769-176	UR	E45171	600	20	16-12
769-176	UR	E45172	300	20	28-12

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected