

MICROPHONE MODEL NUMBER	CABLE‡	CARTRIDGE	SCREEN & GRILLE ASSEMBLY	MIC CLIP	WINDSCREEN	MISCELLANEOUS ACCESSORIES
Super55		R115S				
55SH Series II		R115				DST=S37A
450 Series II	C31C	R96				SW=RK141S
512		R93				SW=A120S
514B	C25C	R103				M=RK6MB
515BSM		R180	RK334G	A25D	A1WS	G12, G18, G12B, G18B, G27B
515BSLX		R180	RK334G	A25D	A1WS	G12, G18, G12B, G18B, G27B
515SBGX		R180	RK334G	A25D	A1WS	F=A12, A13HD
515SBG-18X		R180	RK334G	A25D	A1WS	G12, G18, G12B, G18B, G27B
515SBG-18XF		R180	RK334G	A25D	A1WS	G12, G18, G12B, G18B, G27B
515SDX		R180	RK333G	A25D	A1WS	SMT=A55M, A55HM; M=A26M; DST=S37A
520DX		R198				
522	C31C	R98				SW=RK141S
527B	C29C	R131				M=RK6MB, SW=RK319S
527C	C30C	R132				M=RK6MB, SW=RK319C
545SD-LC		R45	RK244G	A25D	A2WS	SMT=A55M, A55HM; DST=S37A, M=A26M
561		R50	RK85G			G=G12, G18, G6A, G18A F=A12, A13HD
562		R90				G=G12, G18, G6A, G18A; F=A12, A13HD
577B	C117	R98B				M=RK6MB, SW=RK338S
588SDX		R180	RK332G	A25D	A58WS	SMT=A55M, A55HM; DST=S37A
BETA 27				A32M	A32WS	A27ZB
BETA 52A		R175	RK321			
BETA 53			RPM208, RPM212 RPM214, RPM220		RPM304, RPM306	PA=RPM626; RPM132 (Black) BO=RPM134 (Tan) CA=95B2234
BETA 54			RPM208, RPM212		RPM316, RPM318	PA=RPM626; BO=RPM646 (Black) RPM134 (Tan); CA=95B2234
BETA 56A		R174	RK320		A1WS	DM=A56D
BETA 57A		R174	RK320	A25D	A1WS; A57AWS	SMT=A55M, A55HM; DST=S37A; DM=A56D
BETA 58A		R176	RK265G	A25D	A58WS	SMT=A55M, A55HM; DST=S37A
BETA 87A		R193	RK312	A25D	A85WS	SMT=A53M, A55HM
BETA 87C		RPM118	RK312	A25D	A85WS	SMT=A53M, A55HM
BETA 91A	C25E	RPM98A/C				PA=RPM626; RPM622
BETA 98A/C	C98D	RPM98A/C		RK282	RK183WS	HC=A98KCS, DM=A98D, PA=RPM626
BETA 98AD/C	C98D	RPM98A/C		RK282	RK183WS	DM=A98D, PA=RPM626
BETA 98H/C		RPM108, RPM110			RK183WS	PA=RPM440
BETA 181		RPM181/C, RPM181/S, RPM181/O, RPM181/BI		A57F	A181WS	A181C
KSM9/CG		RPM160	RPM262	A25E	A85WS	
KSM9/SL		RPM160	RPM260	A25E	A85WS	
KSM137/SL		RPM116		A57F	A100WS	SMT=A53M
KSM141/SL		RPM116		A57F	A100WS	SMT=A53M
KSM32/SL		RK374	RK371		A32WS, PS-6	M=A32M; SMT=A32SM; CA=A32SC, A32ZB
KSM32/CG		RK374	RK372		A32WS, PS-6	M=A32M; SMT=A32SM; CA=A32SC, A32ZB
KSM42					A32WS	A42SM; A42PF; A42OR; A42SC; A42VB
KSM44A				A44AM		A44ASM; A44ASC; A44AVB
KSM313						SMT=A313M
KSM353						SMT=A353M
MX180/N	C122	R185B, R184B, R183B				TB=RK183T1, RK183T2; PA=RK100PK
MX183	C122	R183B			RK183WS	TB=RK183T1, RK183T2; PA=RK100PK
MX184	C122	R184B			RK183WS	TB=RK183T1, RK183T2; PA=RK100PK
MX185	C122	R185B			RK183WS	TB=RK183T1, RK183T2; PA=RK100PK
MX202B/C,S,N		R185B, R184B, R183B			RK183WS	DST=A202BB; PA=RK100PK
MX202BP/C,S,N		R185B, R184B, R183B			RK183WS	

Microflex® Models
POLAR PATTERN
C=Cardioid
S=Supercardioid
O=Omnidirectional
N=No Cartridge

CARTRIDGE
R185B, R185W
R184B, R184W
R183B, R183W

Accessories Codes
BA=BATTERY
BC=BELT CLIP
BO=BOOM ASSEMBLY
CA=CASE
DM=DRUM MOUNT
DST=DESK STAND

F=FLANGE
G=GOOSENECK
HC=HORN CLAMP
M=SPECIAL MIC MOUNT
PA=PREAMPLIFIER

PL=PLUG ELEMENT
SMT=SHOCK MOUNT
SW=SWITCH
TB=TIE BAR

WIRED MICROPHONE ACCESSORIES & PARTS MATRIX

MICROPHONE MODEL NUMBER	CABLE‡	CARTRIDGE	SCREEN & GRILLE ASSEMBLY	MIC CLIP	WINDSCREEN	MISCELLANEOUS ACCESSORIES
MX202W/C,S,N		R185W, R184W, R183W			95B2064	DST=A202BB, PA=RK100PK
MX202WP/C,S,N		R185W, R184W, R183W			95B2064	
MX391/C,S,O	C123	R185B, R184B, R183B				PA=RK100PK
MX391W/C,S,O		R185W, R184W, R183W				
MX392/C,S,O	C130	R185B, R184B, R183B				
MX393/C,S,O	C129	R185B, R184B, R183B				
MX412/C,S,N		R185B, R184B, R183B		A57F	RK412WS, A99WS, A412MWS	SMT=A400SM; M=A412B
MX418/C,S,N		R185B, R184B, R183B		A57F	RK412WS, A99WS, A412MWS	SMT=A400SM; M=A412B
MX412D/C,S,N		R185B, R184B, R183B			RK412WS, A99WS, A412MWS	
MX418D/C,S,N		R185B, R184B, R183B			RK412WS, A99WS, A412MWS	
MX412S/C,S,N		R185B, R184B, R183B		A57F	RK412WS, A99WS, A412MWS	SMT=A400SM; M=A412B;
MX418S/C,S,N		R185B, R184B, R183B		A57F	RK412WS, A99WS, A412MWS	SMT=A400SM; M=A412B
MX412SE/C,S,N		R185B, R184B, R183B			RK412WS, A99WS, A412MWS	SMT=A400SM; PA=RK100PK
MX418SE/C,S,N		R185B, R184B, R183B			RK412WS, A99WS, A412MWS	SMT=A400SM; PA=RK100PK
PG27-LC					A32WS	SMT=A27SM
PG27-USB					A32WS	SMT=A27SM
PG42-LC					A32WS	SMT=A27SM
PG42-USB					A32WS	SMT=A27SM; SMT=A278M
PG48			95A2207C	A25D	A58WS	SMT=A55HM, A55M
PG52		RPM154				
PG56		RPM152			A85WS	DM=A50D
PG57		RPM152		A25D	A85WS	SMT=A55HM, A55M; DM=A56D
PG58		RPM150		A25D	A58WS	SMT=A55HM, A55M
PG81				A25D	A3WS	SMT=A55HM, A55M
SM2	C108	R93			RK184WS	
SM7B		RPM106			A7WS, RK345	DST=S37A
SM10A-CN		R93			RK184WS	SW=A120S; BC=RK200BC
SM11-CN	C91	R99				SW=A120S; TB=RK203TC; M=RK279; BC=RK200BC
SM27-LC				A32M	PS-6, A32WS	SM=A27SM; CA=A32ZB, A32SC
SM48-LC		R136	RK248G	A25D	A58WS	SMT=A55M, A55HM; DST=S37A
SM48S-LC		R136	RK248G	A25D	A58WS	SMT=A55M, A55HM; PL=RK40P; DST=A37A,
SM57-LC		R57	RK244G	A25D	A2WS	M=A26M.; SMT=A55M, A55HM; PL=RK40P, DM=A56D
SM57-X2U		R57	RK244G	A25D	A2WS	
SM58-CN		R59	RK143G	A25D	A58WS	SMT=A55M, A55HM; DST=S37A
SM58-LC		R59	RK143G	A25D	A58WS	SMT=A55M, A55HM; DST=S37A
SM58S		R59	RK143G	A25D	A58WS	SMT=A55M, A55HM; DST=S37A
SM58-X2U		R59	RK143G	A25D	A58WS	SMT=A55M, A55HM
SM63		R191	RK366G	A57F	RK229WS	SMT=A53M; DST=S37A
SM63L		R191	RK367G	A57F	RK229WS	SMT=A53M; DST=S37A
SM63LB		R191	RK368G	A57F	49A130	SMT=A53M; DST=S37A
SM81-LC		RK104		A57F	A81WS	SMT=A53M
SM86		RPM112	RPM226	A25D	A85WS	SMT=A55M, A55HM
SM87A		R128	RK214G	A25D	A85WS	SMT=A55M, A55HM
SM89				A57F	RK257WS	SMT=A89SM
SM93					RK355WS	TB=RK354SB (Black)
SM94-LC				A25D	A3WS	SMT=A55M
SM137-LC				A25D	A3WS	SMT=A55M
VP64A		R199		A57F	49A130	
VP64AL		R199		A57F	49A130	
VP88	95A2300					SMT=A88SM; BA=80A463
WH20XLR					RK318WS	
WH30XLR		R185B, R184B, R183B				PA=RPM420

Microflex® Models

POLAR PATTERN

C=Cardioid O=Omnidirectional
S=Supercardioid N=No Cartridge

CARTRIDGE

R185B, R185W, R184B
R184W, R183B, R183W

Accessories Codes

BA=BATTERY
BC=BELT CLIP
BO=BOOM ASSEMBLY
CA=CASE

DM=DRUM MOUNT

DST=DESK STAND
F=FLANGE
G=GOOSENECK

HC=HORN CLAMP

M=SPECIAL MIC MOUNT
PA=PREAMPLIFIER
PL=PLUG ELEMENT

PS=POWER SUPPLY

SMT=SHOCK MOUNT
SW=SWITCH
TB=TIE BAR

SHURE[®]
LEGENDARY
PERFORMANCE™

United States, Canada,
Latin America, Caribbean:
Shure Incorporated
5800 West Touhy Avenue
Niles, IL 60714-4608 USA

Phone: 847-600-2000
Fax: 847-600-1212 (USA)
Fax: 847-600-6446
Email: info@shure.com

Europe, Middle East, Africa:

Shure Europe GmbH
Jakob-Dieffenbacher-Str. 12,
75031 Eppingen, Germany

Phone: 49-7262-92490
Fax: 49-7262-9249114
Email: info@shure.de

Asia, Pacific:

Shure Asia Limited
22/F, 625 King's Road
North Point, Island East
Hong Kong

Phone: 852-2893-4290
Fax: 852-2893-4055
Email: info@shure.com.hk