


7717-178NG

TO-5



Nylon

Leads: 3

Diameter: 8.89

Thickness: 0.53

Material Specifications

Suffix	Base Material	Maximum Operating Temperature		Color
		Continuous	Deflection	
-N	Nylon base resin per ASTM STD D4066-82 PA111	121.0°C 250°F	243.3°C 470°F	Natural
-DAP*	Diallyl Phthalate per MIL-M-14G Type SDG	204.4°C 400°F	282.2°C 540°F	Black only

* All "-DAP" mounting pads meet UL 94V-0

Note: Please specify material for each mounting pad:

"N" = nylon; "Dap" = Diallyl Phthalate.

Example: 7717-3N, 7717-86DAP