


Part Number : **1901X05W**

Type	Size	IP Rating	Description
LED	M8	67	Flat bezel panel indicator without resistor

Dimensions(mm):



Part #	Colour	Voltage(V)	Current(mA)	Intensity(mcd typ)
1901X05W	Cool white	3.3Vdc	30 max	500(@ 20mA)

Notes:

1. Bezel codes : X=0(satin),1(black),or 2(matt) chrome
2. Storage temperature -25 °C to +80°C
3. Application temperature -20 °C to +60°C
4. Terminals: Brass +ve, Tinned brass -ve
5. Terminals not qualified for soldering
6. The plastic(polycarbonate) has limited chemical resistance
7. Sealed to IP67 when used with the supplied gasket
8. RoHS & REACH SVHC compliant

Issue # 1 : 8 Feb 12