


Part Number : **1904X00W**

Type	Size	IP Rating	Description
LED	M8	40	Prominent bezel panel indicator w/o resistor

Dimensions(mm):



Part #	Colour	Voltage(V)	Current(mA)	Intensity(mcd typ)
1904X00W	Cool white	3.2Vdc	30 max	500(@ 20mA)

Notes:

1. Bezel codes : X=0(satin),1(black),or 2(matt) chrome
2. Storage temperature -25 °C to +80°C
3. Application temperature -20 °C to +60°C
4. The plastic(polycarbonate) has limited chemical resistance
5. RoHS & REACH SVHC compliant

Issue # 1 : 10 Feb 12