


Part Number : **1905XXZW**

Type	Size	IP Rating	Description
LED	M8	67	Recessed bezel panel indicator

Dimensions(mm):



Part #	Colour	Voltage	Current(mA)	Intensity(mcd typ)
1905X2ZW	Cool white	12VAC/DC	8/15	400
1905X3ZW	Cool white	24VAC/DC	8/15	400

**Notes:**

1. Bezel codes : X=0(satin),1(black),or 2(matt) chrome
2. Light intensity reduced by ~25% on AC
3. Storage temperature -25 °C to +80°C
4. Application temperature -20 °C to +60°C
5. Terminals: Brass +ve, Tinned brass -ve
6. Terminals not qualified for soldering
7. The plastic(polycarbonate) has limited chemical resistance
8. Sealed to IP67 when used with the supplied gasket
9. RoHS & REACH SVHC compliant

Issue # 1 : 10 Feb 12