




**Panel Mount Indicator, Non-Relampable  
Neon and Incandescent Technology  
Mounting Hole, Ø 0.310"**



All dimensions are in inches



Minimum panel thickness: 0.030"

6" leads with 1/2" strip are standard

Storage temperature  $T_{STG}$  : -25°C - +80°C  
 Ambient temperature  $T_A$  : -20°C - +60°C  
 Voltage tolerance  $V_{OP}$  : ±10%

Part No.	Lens Color	Voltage	Current mA	Rated Life
<b>Neon 115VAC Series</b>				
WL-2110A1	Red	105-125VAC	1.5mA	25,000 Hrs
WL-2110A2	Clear	105-125VAC	1.5mA	25,000 Hrs
WL-2110A3	Amber	105-125VAC	1.5mA	25,000 Hrs
WL-2110A4	White	105-125VAC	1.5mA	25,000 Hrs
WL-2112A5	Green	105-125VAC	1.5mA	25,000 Hrs
WL-2112A6	Blue	105-125VAC	1.5mA	25,000 Hrs
<b>Neon 230VAC Series</b>				
WL-2111A1	Red	208-250VAC	1.5mA	25,000 Hrs
WL-2111A2	Clear	208-250VAC	1.5mA	25,000 Hrs
WL-2111A3	Amber	208-250VAC	1.5mA	25,000 Hrs
WL-2111A4	White	208-250VAC	1.5mA	25,000 Hrs
WL-2113A5	Green	208-250VAC	1.5mA	25,000 Hrs
WL-2113A6	Blue	208-250VAC	1.5mA	25,000 Hrs
<b>Incandescent 12V Series</b>				
WL-2195A1-12V	Red	12V-14V	80mA	25,000 Hrs
WL-2195A3-12V	Amber	12V-14V	80mA	25,000 Hrs
WL-2195A4-12V	White	12V-14V	80mA	25,000 Hrs
WL-2195A5-12V	Green	12V-14V	80mA	25,000 Hrs
<b>Incandescent 28V Series</b>				
WL-2195A1-28V	Red	24V-28V	40mA	25,000 Hrs
WL-2195A3-28V	Amber	24V-28V	40mA	25,000 Hrs
WL-2195A4-28V	White	24V-28V	40mA	25,000 Hrs
WL-2195A5-28V	Green	24V-28V	40mA	25,000 Hrs

Body Material: Nylon, white  
 Lens Material: Polycarbonate  
 Bezel Material: Nylon, white  
 Wire Gauge: 18 AWG  
 Wire Strip: 1/2"

Certifications: Most Wamco indicators carry Agency approvals. Please contact Wamco for the latest Agency information regarding the specific product series and voltage required.  
 Options: Additional options and lens styles available. Please contact Wamco for more information.

<b>Drawn</b>	SC	03/01/10	<b>Panel Mount Indicators Neon and Incandescent</b>	<b>Datasheet:</b> WL-211XAX Series WL-2195AX-XXX Series	<b>Rev:</b> 1
<b>Checked</b>	EB	03/01/10			
<b>Approved</b>	EB	03/02/10			