

INTRODUCTION

Wamco i-View 501 is an LED lighting system designed for small and medium sized billboards or traffic signs as well as a wall washing of buildings, bridges, sculptures, etc. i-View 501 has much lower power consumption (around 40W including DC power supply) than conventional 150W HQI lamp and Halogen lighting fixtures. i-View 501 provides many advantages including brilliant light output, significant energy cost saving and reduced maintenance costs.



FEATURES

- Energy efficient (up to 75% energy saving compared to 150W HQI or halogen lamps)
- 35W (around 40W including DC power supply) power consumption
- Available in White: 6500K and Warm White: 3300K
- Long service life (up to 40,000 hours)
- Water resistant (outdoor use, **IP65**)
- 3 year warranty



APPLICATIONS

- Lighting for small and medium sized billboards and traffic signs
- Wall washing (buildings, bridges, etc)

CERTIFICATIONS

- CE




SPECIFICATIONS



Model	Model No.	Input Vol.	Power Cons.	CCT	Beam Angle	Lum. Flux
i-View 501 White	WL-B501035W04	24VDC	35W	6500K	110°	2350 lm
i-View 501 Warm White	WL-B501035L04	24VDC	35W	3300K	110°	2300 lm

- Operating Temp.: -20°C ~ +60°C

PHYSICAL SPECIFICATION (Unit: mm)



LIGHT DISTRIBUTION



i-View 501 White (6500K)

INSTALLATION

