



SEARCH

Notice
 Product images illustrated here are intended to represent the product type, and may or may not show the exact part characteristics such as envelope, base, filament, lens type or color. Please contact Wamco for detailed product illustrations and specifications.

- FLUORESCENT
- HALOGEN
- INCANDESCENT
- LED
- NEON
- READOUTS & DISPLAYS

SEARCH RESULTS FOR: WL-L04MR16-W30NF

[← BACK](#)

Showing 1 to 1 of 1 Items

Page: 1

SORT RESULTS BY: [▶](#)

Please select sorting order:

[SORT](#)



WL-L04MR16-W30NF
WL

[INQUIRE](#)

Approvals	UL	Base	GU5.3
Beam Angle	25°	Brightness	230 Lm
CCT	3000K-3200K	Color	WARM WHITE
CRI	82	Envelope	MR16
Notes	NARROW FLOOD	Volts	12V AC/DC
Watts	4W		

Showing 1 to 1 of 1 Items

Page: 1

[← BACK](#) [↑ TOP](#)

