



SEARCH



**Notice**  
 Product images illustrated here are intended to represent the product type, and may or may not show the exact part characteristics such as envelope, base, filament, lens type or color. Please contact Wamco for detailed product illustrations and specifications.

- FLUORESCENT
- HALOGEN
- INCANDESCENT
- LED
- NEON
- READOUTS & DISPLAYS

SEARCH RESULTS FOR: WL-L07PAR20-W30NF


[← BACK](#)

Showing 1 to 2 of 2 Items

Page: 1


SORT RESULTS BY:

Please select sorting order:



**WL-L07PAR20-W30NF**  
**WL** [INQUIRE](#)

Approvals	UL	Base	E26
Beam Angle	25°	Brightness	320 Lm
CCT	2800K-3000K	Color	WARM WHITE
CRI	82	Envelope	PAR20
Notes	NARROW FLOOD, DIMMABLE	Volts	120VAC
Watts	7W		



**WL-L07PAR20-W30NF-P**  
**WL** [INQUIRE](#)

Approvals	UL	Base	E26
Beam Angle	25°	Brightness	338 Lm
CCT	2800K-3000K	Color	WARM WHITE
CRI	82	Envelope	PAR20
Notes	NARROW FLOOD, DIMMABLE	Protection	IP65
Type	OUTDOOR	Volts	120VAC
Watts	7W		

Showing 1 to 2 of 2 Items

Page: 1

[← BACK](#) [↑ TOP](#)

