



by Schneider Electric

List Price \$356.00 USD

Availability **Stock Item: This item is normally stocked in our distribution facility.**

Technical Characteristics

Ampere Rating	10A
General Application	Short circuit and overcurrent protection
Short Circuit Current Rating	10kA@240VAC
For Use With	OEM Panels and Enclosures
Voltage Rating	240VAC
Circuit Breaker Type	Standard
HACR Rated	Yes
Mounting Type	Flush, Surface or DIN Rail (35mm)
Weight	13.10 Ounces
Number of Poles	3-Pole
Approvals	UL489 Listed - CSA 22.2 #5.1 Certified - IEC Rated 60947-2
Enclosure Rating	IP40
Marketing Trade Name	Multi 9
Type	C60N
Wire Size	#18 to #4 AWG
Terminal Type	Line: Box Lug - Load: Box Lug
Depth	3.00 Inches (76mm)
Height	4.21 Inches (107mm)
Trip Curve	C Curve - Magnetic operates between 7 to 10 times
Width	2.13 Inches (54mm)

Shipping and Ordering

Category	00915 -
Discount Schedule	DE2
GTIN	00785901209492
Package Quantity	1
Weight	0.82 lbs.
Availability Code	Stock Item: This item is normally stocked in our distribution facility.
Returnability	Y
Country of Origin	FR

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.

Generated: 03/15/2012 06:08:19