

H0,25/12 HBL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16


D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-2083

www.weidmueller.com



- supplied loose in polybag
- Weidmüller colour code

General ordering data

Order No.	9025760000
Type	H0,25/12 HBL
Version	Wire end ferrule, 0.25 mm ² , 8 mm, Colour code: Weidmüller, Light blue
GTIN (EAN)	4008190010027
Qty.	500 pc(s).

H0,25/12 HBL

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-2083
 www.weidmueller.com

Technical data

Dimensions

Length 12 mm

Product data

Conductor cross-section	0.25 mm ²	Contact surface length (L2)	8 mm
Contact surface diameter (D1)	0.8 mm	Collar diameter (D2)	1.8 mm
Metal sleeve thickness (S1)	0.15 mm	Plastic collar thickness (S2)	0.25 mm

Classifications

ETIM 2.0	EC000005	ETIM 3.0	EC000005
ETIM 4.0	EC000005	UNSPSC	31-16-31-02
eClass 4.1	27-06-07-01	eClass 5.1	27-40-02-01
eClass 6.0	27-40-02-01	eClass 7.0	27-40-02-01

Product information

Description of article Wire end ferrule with plastic collar, light blue

Approvals

Approvals

