




LP2N 5.08/90



Technical data	VDE	UL	CSA
Rated voltage (V)	250*	300	300
Rated current (A)	24	15	20
Wire size (mm ² /AWG)	4.0	26...12	26...12


*Pollution severity 3 / Overvoltage category III
Additional technical data see page 58

Solder pin length 4.5 mm 4.5 mm

Color		Part No.	Part No.	Qty.
4	LP2N 5.08/4/90	1635150000	1695900000	50
6	LP2N 5.08/6/90	1625550000	1695910000	50
8	LP2N 5.08/8/90	1596470000	-	
10	LP2N 5.08/10/90	1596500000	-	
12	LP2N 5.08/12/90	1632560000	-	
14	LP2N 5.08/14/90	1632570000	-	
16	LP2N 5.08/16/90	1596520000	-	
18	LP2N 5.08/18/90	1632580000	-	
20	LP2N 5.08/20/90	1596560000	-	
22	LP2N 5.08/22/90	1632590000	-	
24	LP2N 5.08/24/90	1596600000	-	
26	LP2N 5.08/26/90	1632600000	-	
28	LP2N 5.08/28/90	1632610000	-	
30	LP2N 5.08/30/90	1596640000	-	
32	LP2N 5.08/32/90	1632620000	-	
34	LP2N 5.08/34/90	1632630000	-	
36	LP2N 5.08/36/90	1632640000	-	
38	LP2N 5.08/38/90	1632650000	-	
40	LP2N 5.08/40/90	1632660000	-	
42	LP2N 5.08/42/90	1632670000	-	
44	LP2N 5.08/44/90	1632680000	-	
46	LP2N 5.08/46/90	1632690000	-	
48	LP2N 5.08/48/90	1632700000	-	

Accessories	Page
Marking	40
Mounting	46
Miscellaneous	43, 45, 46

LP2H 5.08/90



Technical data	VDE	UL	CSA
Rated voltage (V)	250*	300	300
Rated current (A)	24	15	20
Wire size (mm ² /AWG)	4.0	26...12	26...12


*Pollution severity 3 / Overvoltage category III
Additional technical data see page 58

Solder pin length 4.5 mm 4.5 mm

Color		Part No.	Part No.	Qty.
4	LP2H 5.08/4/90	1668630000	1697320000	50
6	LP2H 5.08/6/90	1625590000	1697330000	50
8	LP2H 5.08/8/90	1596690000	-	
10	LP2H 5.08/10/90	1596710000	-	
12	LP2H 5.08/12/90	1632860000	-	
14	LP2H 5.08/14/90	1632870000	-	
16	LP2H 5.08/16/90	1596730000	-	
18	LP2H 5.08/18/90	1632880000	-	
20	LP2H 5.08/20/90	1596750000	-	
22	LP2H 5.08/22/90	1632890000	-	
24	LP2H 5.08/24/90	1596770000	-	
26	LP2H 5.08/26/90	1632900000	-	
28	LP2H 5.08/28/90	1632910000	-	
30	LP2H 5.08/30/90	1596790000	-	
32	LP2H 5.08/32/90	1632920000	-	
34	LP2H 5.08/34/90	1632930000	-	
36	LP2H 5.08/36/90	1632940000	-	
38	LP2H 5.08/38/90	1632950000	-	
40	LP2H 5.08/40/90	1632960000	-	
42	LP2H 5.08/42/90	1632970000	-	
44	LP2H 5.08/44/90	1632980000	-	
46	LP2H 5.08/46/90	1632990000	-	
48	LP2H 5.08/48/90	1633000000	-	

Accessories	Page
Marking	40
Mounting	-
Miscellaneous	43, 45

LP2HR 5.08/90



Technical data	VDE	UL	CSA
Rated voltage (V)	250*	300	300
Rated current (A)	24	15	20
Wire size (mm ² /AWG)	4.0	26...12	26...12

*Pollution severity 3 / Overvoltage category III
Additional technical data see page 58

Solder pin length 4.5 mm 4.5 mm

Color		Part No.	Part No.	Qty.
4	LP2HR 5.08/4/90	1636290000	1697340000	50
6	LP2HR 5.08/6/90	1636300000	1697350000	50
8	LP2HR 5.08/8/90	1636310000	-	
10	LP2HR 5.08/10/90	1636320000	-	
12	LP2HR 5.08/12/90	1668640000	-	
14	LP2HR 5.08/14/90	1668650000	-	
16	LP2HR 5.08/16/90	1636330000	-	
18	LP2HR 5.08/18/90	1668660000	-	
20	LP2HR 5.08/20/90	1636340000	-	
22	LP2HR 5.08/22/90	1668670000	-	
24	LP2HR 5.08/24/90	1636350000	-	
26	LP2HR 5.08/26/90	1668680000	-	
28	LP2HR 5.08/28/90	1668690000	-	
30	LP2HR 5.08/30/90	1636360000	-	
32	LP2HR 5.08/32/90	1668700000	-	
34	LP2HR 5.08/34/90	1668710000	-	
36	LP2HR 5.08/36/90	1668720000	-	
38	LP2HR 5.08/38/90	1668730000	-	
40	LP2HR 5.08/40/90	1668740000	-	
42	LP2HR 5.08/42/90	1668750000	-	
44	LP2HR 5.08/44/90	1668760000	-	
46	LP2HR 5.08/46/90	1668770000	-	
48	LP2HR 5.08/48/90	1668780000	-	

Accessories	Page
Marking	40
Mounting	-
Miscellaneous	43, 45