

---

Item no.: 262-331  
Product description: 4-CONDUCTOR TERMINAL BLOCK FOR SCREW OR  
SIMILAR MOUNTING TYPES 3.2 MM Ø MOUNTING ADAPTER  
AVAILABLE FOR TS 35 (209-123)

---



Produkt kann von Bild abweichen / product may differ

Packing unit 100 2\*50 pieces

RoHS compliant

Product group	9 (Std Chassis Mt Blocks)
Cross section [mm <sup>2</sup> ]	0.08 - 4 mm <sup>2</sup>
Cross section [AWG]	28 - 12 AWG
Connection method	CAGE CLAMP® CONNECTION
Measured voltage EN	630 V
Measured shock voltage	8 kV
Pollution degree	3
Current intensity EN	32 A
Weight	6.83 g
Color	gray
Wiring type	Side-entry
No. of connection Points	4
No. of potentials	1
Height	23 mm
Height	0.906 in
Width	12 mm
Width	0.472 in
Depth	33.5 mm

Depth	1.32 in
Strip length from	9 mm
Strip length to	10 mm
Strip length	0.37 in



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [ mm <sup>2</sup> ]
262-331	ABS	04-HG476174/1-PDA	630	32	4
262-331	BV	07436/C0			0,08-4
262-331	CCA	NL6510	630	32	0,08-4
262-331	CSA	18677-45	300	20	26-12
262-331	DNV	E-9215	630	32	4
262-331	GL	17295-00HH	630	32	4
262-331	KEMA	2110272.03	630	24	0,08-4
262-331	KR	HMB05880-EL002	630	32	32
262-331	LR	92/20242(E5)	630	24	4
262-331	PRS	TE/1718/880590/08	630		0,08-4
262-331	RMR	11130002	630	32	4
262-331	UR	E45172	300	20	28-12

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected