



The Airflow is the original quick-release coupling with over 50 years of design enhancements, and is manufactured in the UK to the highest standards.

**Designed for FIXED applications.**

### Key Product Benefits

- Compatible with the Standard range of Adaptors
- Steel Construction - robust and hardwearing, ideal for use in the engineering/workshop environment
- Positive locking mechanism

### Specifications

**Nominal bore:** 4.8mm

**Maximum flow rate:** 43cfm @ 100lbf/in<sup>2</sup>

**Maximum Working Pressure:** 200lbf/in<sup>2</sup> (14bar)

**Type:** Single Action

### Interchangeability

Rectus 19

### Product Options

Part No.	Description	Thread Type	Thread Size
AC21CM	Airflow Coupling	Male	R 1/4
AC21EM	Airflow Coupling	Male	R 3/8
AC21JM	Airflow Coupling	Male	R 1/2
AC21CF	Airflow Coupling	Female	Rp 1/4
AC21EF	Airflow Coupling	Female	Rp 3/8
AC21JF	Airflow Coupling	Female	Rp 1/2
AC21R	Airflow Coupling	Hose Tailpiece	7mm (1/4")
AC21S	Airflow Coupling	Hose Tailpiece	8mm (5/16")
AC21T	Airflow Coupling	Hose Tailpiece	10mm (3/8")
AC21CM05	Airflow Coupling - Display Packed	Male	R 1/4
AC21EM05	Airflow Coupling - Display Packed	Male	R 3/8
AC21JM05	Airflow Coupling - Display Packed	Male	R 1/2
AC21CF05	Airflow Coupling - Display Packed	Female	Rp 1/4
AC21EF05	Airflow Coupling - Display Packed	Female	Rp 3/8
AC21JF05	Airflow Coupling - Display Packed	Female	Rp 1/2
AC21R05	Airflow Coupling - Display Packed	Hose Tailpiece	7mm (1/4")
AC21S05	Airflow Coupling - Display Packed	Hose Tailpiece	8mm (5/16")
AC21T05	Airflow Coupling - Display Packed	Hose Tailpiece	10mm (3/8")