



## Metric Spacers

### Clearance spacers

- Special body lengths can be specified, by modifying the order code. For example, R30-601xx02, xx denotes body length in mm.
- Please contact technical@harwin.com for further information.
- Brass spacers: base material is free-machining brass, with nickel plating.
- Aluminium spacers: supplied with a chromate conversion protective coating.



Brass, circular



Aluminium, circular



Plastic, circular

## HOW TO ORDER

SERIES CODE	R	XX	-	XXX	XX	XX
R30-601						
R30-620						
R30-670						
R40-600						
R40-661						
R40-671						

MATERIAL/FINISH	
00	Plastic (R40-661)
02	Brass/Nickel
14	Aluminium/Chromate
94	Plastic (R30-670, R40-671)

LENGTH (mm)
03 to 16, 18, 20, 25, 30

[www.harwin.com](http://www.harwin.com)

All dimensions in mm.



**HARWIN**

# Customer Information Sheet

DRAWING No.: R40-671XX94

SHEET 2 OF 2

IF IN DOUBT - ASK



(C)

NOT TO SCALE

THIRD ANGLE PROJECTION

ALL DIMENSIONS IN mm

PART No.	L
R40-6710394	3.00
R40-6710494	4.00
R40-6710594	5.00
R40-6710694	6.00
R40-6710794	7.00
R40-6710894	8.00
R40-6710994	9.00
R40-6711094	10.00
R40-6711194	11.00
R40-6711294	12.00
R40-6711394	13.00
R40-6711494	14.00
R40-6711594	15.00
R40-6711694	16.00
R40-6711894	18.00
R40-6712094	20.00
R40-6712594	25.00
R40-6713094	30.00



ORDER CODE:

**R40-671XX94**

LENGTH L IN mm \_\_\_\_\_

CP	4	24.02.10	10676
NAME	ISS.	DATE	C/NOTE
APPROVED: C.PENROSE			
CHECKED: R.ADDE			
DRAWN: A.J.F			
CUSTOMER REF.:			
ASSEMBLY DRG.:			

**HARWIN**

 HARWIN USA  
 TEL: 603 893 5376  
 FAX: 603 893 5396  
 mis@harwin.com

 HARWIN Europe (UK)  
 TEL: 023 9231 4545  
 FAX: 023 9231 4590  
 mis@harwin.co.uk

 HARWIN Asia  
 TEL: +65 6 779 4909  
 FAX: +65 6 779 3868  
 mis@harwin.com.sg

THIS DRAWING AND ANY INFORMATION OR DESCRIPTIVE MATTER SET OUT HEREON ARE CONFIDENTIAL AND COPYRIGHT PROPERTY OF THE HARWIN GROUP AND MUST NOT BE DISCLOSED, LOANED, COPIED OR USED FOR MANUFACTURING, TENDERING OR FOR ANY OTHER PURPOSE WITHOUT THEIR WRITTEN PERMISSION.

 TOLERANCES  
 X. = ±1mm  
 X.X = ±0.25mm  
 X.XX = ±0.10mm  
 X.XXX = ±0.01mm  
 ANGLES = ±5°  
 UNLESS STATED

 MATERIAL:  
 NYLON 66 - WHITE  
 FINISH: CLEAN  
 S/AREA: mm<sup>2</sup>

 TITLE:  
 M4 CLEARANCE CIRCULAR SPACER  
 DRAWING NUMBER:  
**R40-671XX94**  
 2 OF 2