



by Schneider Electric

List Price \$107.00 USD

Availability **Non-Stock Item: This item is not normally stocked in our distribution facility.**

Technical Characteristics

Timing Range	0.3 - 30 Minutes
Type	JCK
Approvals	UL Listed File Number E78351 CCN NLDX - CSA Certified File Number 214768 Class 321107 - CE Marked
Features	Up to +/- 0.1 Percentage Repeat Accuracy; Transient Protected; Variable or Fixed Time Delay; Available in 5 timing modes.
Contact Break	3A@120VAC, 1.5A@240VAC
Horsepower Rating	1/3HP@120VAC - 1/2HP@240VAC
Contact Arrangement	DPDT
Maximum Voltage Rating	240VAC
Mounting Type	Socket
Contact Configuration	2 N.O./2 N.C.
Number of Pins	11 Pin
Contact Make	30A@120VAC, 15A@240VAC
Timing Mode	Off Delay
Ampere Rating	10A
Coil Voltage	24V
Type of Pins	Tubular

Shipping and Ordering

Category	21651 - Timers, Plug-In, Type JCK (Excludes JCK60 & 70)
Discount Schedule	CP2
GTIN	00785901094685
Package Quantity	1
Weight	0.3 lbs.
Availability Code	Non-Stock Item: This item is not normally stocked in our distribution facility.
Returnability	N
Country of Origin	US

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.