



# FLEXI-SMA90-433


- $\frac{1}{4}$  Wavelength Whip Antenna
- Rugged Flexible Plastic Finish.
- Available as BNC, SMA-Plug, M4 Screw Fixing
- Available as Straight or Right Angle
- VSWR < 2.0
- 50ohm Impedance
- Operating Temp -30 to +60°C
- Insulation resistance 500M $\Omega$  @500Vdc



## Applications

- General Low Power Radio

## Mechanical Dimensions





# FLEXI-SMA90-433

## Performance / VSWR Plot



R F Solutions Ltd.,  
Unit 21, Cliffe Industrial Estate,  
Lewes, E. Sussex. BN8 6JL. England.

Email : [sales@rfsolutions.co.uk](mailto:sales@rfsolutions.co.uk) <http://www.rfsolutions.co.uk>

Tel: +44 (0)1273 898 000 Fax: +44 (0)1273 480 661

