

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0430300006**
Status: **Active**
Overview: [microfit_30](#)
Description: Micro-Fit 3.0™ Crimp Terminal, Female, with Select Gold (Au) Plated Phosphor Bronze Contact, 26-30 AWG, Reel

Documents:

[3D Model](#) [Test Summary TS-43045-002 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-43045 \(PDF\)](#)

General

Product Family	Crimp Terminals
Series	43030
Application	Power
Crimp Quality Equipment	Yes
Overview	microfit_30
Product Literature Order No	987650-5984
Product Name	Micro-Fit 3.0™


Physical

Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Packaging Type	Reel
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.27mm max.
Wire Size AWG	26, 28, 30
Wire Size mm²	N/A

Material Info

Reference - Drawing Numbers

Product Specification	PS-43045, RPS-43045-003, RPS-43045-004
Sales Drawing	SD-43030-****
Test Summary	TS-43045-002



EU RoHS

ELV and RoHS Compliant
REACH SVHC Contains SVHC: No Low-Halogen Status Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[43030Series](#)

Use With

43025 Receptacle Housing, 43645 Receptacle Housing, [44133](#) Panel Mount Receptacle Housing

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Insertion Tool for Crimp Terminal	0638120800
FineAdjust™ Applicator for insulation OD 1.12-1.27mm - 26-30 AWG	0639004400
FineAdjust™ Applicator for	0639001600

insulation OD
0.63-1.10mm - 26-30
AWG
T2 Terminator™ 0639104400
for insulation OD
1.12-1.27mm - 26-30
AWG
Hand Crimp Tool 0638190000
Extraction Tool 0011030043

Japan

Description	Product #
Applicator for M211A	<u>0572983000</u>
Bench Press, 20-30 AWG Wire	

This document was generated on 03/08/2012

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION