

Data Sheet



Model 1740B



Model 1743B

B+K Precision models 1744A and 1745A are 0 to 35V, 0 to 10A DC Power Supply. These power supplies have all of the great features you would expect B+K Precision power supplies to have and some new features not normally seen on power supplies in this price range. The output-shorting button allows the user to short the output terminals to set the current limit.

Specifications

	1740B	1743B	1746B	1744A	models 1745A
Output Voltage	0-60 V	0-35 V	0-16 V	0-35V	0-35V
Output Current	0-4 A	0-6 A	0-10A	0-10A	0-10A
Constant Voltage Operation					
Voltage Regulation					
Line (120VAC ± 10%)	≤ 0.2% + 2mV				
Load (no load - full load)	≤ 0.04% + 2mV				
Recovery Time	≤ 100 μs				
Ripple & Noise	1 mV rms (Typical)				
Temperature Coefficient	≤ 300 ppm/°C				
Constant Current Operation					
Adjustable Current Limit	5% to 100%				
Current Regulation					
Line (120VAC ± 10%)	≤ 0.4% + 5mA				
Load	≤ 0.4% + 5mA				
Current Ripple	≤ 3mA rms				
Metering					
Type	2-Analog	Dual 4-digit LED	2-Analog	2-Analog	Dual 4-digit LED
Voltmeter Range	0-64V	0-99.99V (green)	0-16V	0-40V	0-99.99V
Voltmeter Accuracy	± 2.5%	± (0.5% rdg + 9 digits)	± 2.5%	+ 2.5%	± (0.7% + 9 digits)
Ammeter Range					
High Range	0-4.4 A	0-9.999 A (red)	0-11 A	0-11 A	0-9.999
Low Range	0-1.1 A	--	0-2.2 A	0-2.2 A	--
Ammeter Accuracy	± 2.5%	± (0.5% rdg + 9 digits)	± 2.5%	± 2.5%	± 0.7% + 9 digits
Overload Protection	Current limiting, reverse polarity, overvoltage, short circuit				
Power Requirements	120/220 VAC ± 10%, 50/60 Hz				
Power Consumption	450W	420W	380W	560W	560W
Operating Temperature	32° to 104°F (0° to 40°C), ≤ 75% R.H.				
Storage Temperature	5° to 158°F (-15° to +70°C), ≤ 85% R.H.				

- Largest selection of voltage and current ratings ever offered
- Connect two supplies in parallel to double the current output
- Connect two supplies in series to double the voltage output
- Reliable, Durable
- Operate continuously at full load without overheating
- Fully overload protected
- Coarse and fine voltage controls
- Excellent regulation
- Very low ripple
- Constant voltage or constant current operation
- Continuously monitor voltage and current output on two meters

B&K Precision Corporation

22820 Savi Ranch Parkway, Yorba Linda, CA 92887
Tel: 714-921-9095, Fax: 714-921-6422
www.bkprecision.com

Specifications subject to change without notice