

FLUORESCENT LAMPS

TuffGuard Lamps

Watts	Product Number	Symbols, Footnotes	Ordering Code	Pkg. Qty.	Color Temp. (K)	Nom. Length (In.)	Rated Avg. Life (Hrs.)(202)	Approx. Initial Lumens (203,204)	CRI	Availability
-------	----------------	--------------------	---------------	-----------	-----------------	-------------------	-----------------------------	----------------------------------	-----	--------------

TUFFGUARD T12 FLUORESCENT COATED LAMPS

T12 Medium Bipin Linear Fluorescent Lamps

14	I6792-4		F14T12/CW/TG	30	4100	15	9000	710	59	Made to Order
15	I6687-6		F15T12/CW/TG	30	4100	18	9000	800	59	Made to Order
20	I6919-3	●	F20T12/D/ALTO TG	30	6500	24	9000	1075	73	Made to Order
	I6300-6	●	F20T12/CW/ALTO TG	30	4100	24	9000	1200	59	Stocked
25	I6729-6		F25T12/CW/TG	30	4100	36	7500	1900	59	Made to Order
30	I6893-0	●	F30T12/D/RS/ALTO TG	30	6500	36	24,000	1950	73	Made to Order
	I6310-5	●	F30T12/CW/RS/ALTO TG	30	4100	36	24,000	2250	59	Stocked
	I6742-9	●	F48T12/CW/EW/ALTO TG	15	4100	48	9000	2400	59	Made to Order
34	I6032-5	●∅	F34/CW/RS/EW/LL/ALTO TG	30	4100	48	24,000	2650	59	Stocked
	I6060-6	●∅	F34T12/CW/RS/EW/ALTO TG	30	4100	48	20,000	2650	59	Stocked
	I6315-4	●∅	F34T12/WW/RS/EW/ALTO TG	30	3000	48	20,000	2575	49	Stocked
	I6759-3	●∅	F34T12/835/EW/ALTO TG	30	3500	48	20,000	2800	82	Made to Order
	I6764-3	●∅	F34T12/841/EW/ALTO TG	30	4100	48	20,000	2800	82	Made to Order
	I6743-7	●X	F34T12/ADV850/EW/ALTO TG	30	5000	48	24,000	3000	82	Made to Order
	I6693-4	●	F34T12/DX/RS/EW/ALTO TG	30	6500	48	20,000	2025	90	Made to Order
39	I6309-7	●	F48T12/CW/ALTO TG	30	4100	48	9000	2950	59	Stocked
	I6307-1	●	F48T12/D/ALTO TG	15	6500	48	9000	2500	73	Stocked
40	I6736-1	●∅	F40T12/830/ALTO TG	30	3000	48	20,000	3200	82	Made to Order
	I6314-7		F40C50 TG	30	5000	48	20,000	2200	92	Stocked
	I6299-0	●	F40DX/ALTO TG	30	6500	48	20,000	2325	90	Stocked
	I6311-3	●∅	F40T12/835/ALTO TG	30	3500	48	20,000	3200	82	Stocked
	I6322-0	●∅	F40T12/841/ALTO TG	30	4100	48	20,000	3200	82	Stocked
	I6744-5	●∅	F40T12/ADV835/ALTO TG	30	3500	48	24,000	3450	85	Made to Order
	I6918-5	●∅	F40T12/ADV841/ALTO TG	30	4100	48	24,000	3450	85	Made to Order
	I6886-4	●∅	F40T12/ADV850/ALTO TG	30	5000	48	24,000	3300	82	Made to Order
	I6890-6		F40T12/C75 TG	30	7500	48	20,000	2000	95	Made to Order
	20427-1	●∅	F40T12/CW/ALTO TG	30	4100	48	20,000	2650	59	Stocked
56	I6677-7	●	F40T12/CWX/ALTO TG	30	4200	48	20,000	2550	89	Made to Order
	I6689-2	●	F72T12/CW/ALTO TG	15	4100	72	12,000	4450	59	Made to Order
	I6924-3	●	F72T12/D/ALTO TG	15	6500	72	12,000	3800	73	Made to Order

Note: Made to order products require a 3 week lead time.

For the most current product information, go to the e-catalog on www.philips.com

Fluorescent symbols and footnotes located on page 51



T12 Medium Bipin