

Normal Wall Flame Retardant

Heat Shrink Tubing

PRO-POWER
Quality Cables

Features:

- Flexible, general purpose, polyolefin tubing.
- 2:1 shrink ratio.
- Super abrasion and solvent resistance.
- Excellent physical, chemical and electrical properties.
- Wide range of sizes and colours.
- Operating temperature range: -55°C to 125°C.



PRO-POWER
Quality Cables

Normal Wall Flame Retardant Heat Shrink Tubing

PRO-POWER
Quality Cables

Product Dimensions

Size (Inch)	Inside Diameter		Recovered Wall Thickness
	As Supplied	Maximum After Recovery	
3/64	1.0 ±0.2	0.5	0.22 ±0.10
1/16	1.5 ±0.3	0.65	0.28 ±0.10
3/32	2.5 ±0.3	1.00	0.35 ±0.10
1/8	3.5 ±0.4	1.50	0.40 ±0.10
3/16	5.0 ±0.4	2.30	0.50 ±0.10
1/4	6.5 ±0.4	3.00	0.55 ±0.10
3/8	9.5 ±0.5	4.50	0.60 ±0.10
1/2	12.5 ±0.5	6.00	
3/4	19.0 ±0.7	9.00	0.80 ±0.15
1	26.0 ±0.7	12.50	0.90 ±0.15
1-1/4	29.0 ±0.7	14.00	
1-1/2	41.5 ±0.7	20.00	1.00 ±0.15
2	51.0 ±0.7	25.00	
3	≥80	41.00	1.46 ±0.20
4	≥100	51.00	

Dimensions : Millimetres

Product Properties

Physical:

Tensile Strength	: 14.8Mpa.
Elongation	: 460%.
Tensile Strength After Aging	: 14.5Mpa.
Elongation After Aging	: 480%.

Electrical:

Dielectric Strength	: 17KV/mm.
Volume Resistance	: 1 x 10 ¹⁵ Ωcm.

PRO-POWER
Quality Cables

Normal Wall Flame Retardant Heat Shrink Tubing

Part Number Table

Description	Part Number
Heat Shrink Tubing 2:1 Black 1.6 100M	13633
Heat Shrink Tubing 2:1 Black 2.4 100M	13634
Heat Shrink Tubing 2:1 Black 3.2 100M	13635
Heat Shrink Tubing 2:1 Black 4.8 100M	13636
Heat Shrink Tubing 2:1 Black 6.4 100M	13637
Heat Shrink Tubing 2:1 Black 9.50 100M	13638
Heat Shrink Tubing 2:1 Black 12.7 100M	13639
Heat Shrink Tubing 2:1 Black 19 100M	13640
Heat Shrink Tubing 2:1 Black 25.4 50M	13641
Heat Shrink Tubing 2:1 Black 38.1 50M	13642
Heat Shrink Tubing 2:1 Black 50.8 25M	13643
Heat Shrink Tubing 2:1 Black 1.6 5M	13644
Heat Shrink Tubing 2:1 Black 2.4 5M	13645
Heat Shrink Tubing 2:1 Black 3.2 5M	13646
Heat Shrink Tubing 2:1 Black 4.8 5M	13647
Heat Shrink Tubing 2:1 Black 6.4 5M	13648
Heat Shrink Tubing 2:1 Black 9.5 5M	13649
Heat Shrink Tubing 2:1 Black 12.7 5M	13650
Heat Shrink Tubing 2:1 Black 19 5M	13651
Heat Shrink Tubing 2:1 Black 25.4 5M	13652
Heat Shrink Tubing 2:1 Black 38.1 5M	13653
Heat Shrink Tubing 2:1 Black 50.8 5M	13654
Heat Shrink Tubing 2:1 Clear 1.60 100M	13655
Heat Shrink Tubing 2:1 Clear 2.40MM 100M	13656
Heat Shrink Tubing 2:1 Clear 3.20MM 100M	13657
Heat Shrink Tubing 2:1 Clear 4.80MM 100M	13658
Heat Shrink Tubing 2:1 Clear 6.40MM 100M	13659
Heat Shrink Tubing 2:1 Clear 9.50MM 100M	13660
Heat Shrink Tubing 2:1 Clear 12.70MM 100M	13661
Heat Shrink Tubing 2:1 Clear 19.00MM 100M	13662
Heat Shrink Tubing 2:1 Clear 25.40MM 50M	13663
Heat Shrink Tubing 2:1 Clear 38.10MM 50M	13664
Heat Shrink Tubing 2:1 Clear 50.80MM 25M	13665
Heat Shrink Tubing 2:1 Clear 1.60MM 5M	15034

Normal Wall Flame Retardant Heat Shrink Tubing

Part Number Table

Description	Part Number
Heat Shrink Tubing 2:1 Clear 2.40MM 5M	15035
Heat Shrink Tubing 2:1 Clear 3.20MM 5M	15036
Heat Shrink Tubing 2:1 Clear 4.80MM 5M	15037
Heat Shrink Tubing 2:1 Clear 6.40MM 5M	15038
Heat Shrink Tubing 2:1 Clear 9.50MM 5M	15039
Heat Shrink Tubing 2:1 Clear 12.70MM 5M	15040
Heat Shrink Tubing 2:1 Clear 19.00MM 5M	15041
Heat Shrink Tubing 2:1 Clear 25.40MM 5M	15042
Heat Shrink Tubing 2:1 Clear 38.10MM 5M	15043
Heat Shrink Tubing 2:1 Clear 50.80MM 5M	15044
Heat Shrink Tubing 2:1 Red 1.60MM 100M	13666
Heat Shrink Tubing 2:1 Red 2.40MM 100M	13667
Heat Shrink Tubing 2:1 Red 3.20MM 100M	13668
Heat Shrink Tubing 2:1 Red 4.80MM 100M	13669
Heat Shrink Tubing 2:1 Red 6.40MM 100M	13670
Heat Shrink Tubing 2:1 Red 9.50MM 100M	13671
Heat Shrink Tubing 2:1 Red 12.70MM 100M	13672
Heat Shrink Tubing 2:1 Red 19.00MM 100M	13673
Heat Shrink Tubing 2:1 Red 25.40MM 50M	13674
Heat Shrink Tubing 2:1 Red 38.10MM 50M	13675
Heat Shrink Tubing 2:1 Red 50.80MM 25M	13676
Heat Shrink Tubing 2:1 Red 1.60MM 5M	15045
Heat Shrink Tubing 2:1 Red 2.40MM 5M	15046
Heat Shrink Tubing 2:1 Red 3.20MM 5M	15047
Heat Shrink Tubing 2:1 Red 4.80MM 5M	15048
Heat Shrink Tubing 2:1 Red 6.40MM 5M	15049
Heat Shrink Tubing 2:1 Red 9.50MM 5M	15050
Heat Shrink Tubing 2:1 Red 12.70MM 5M	15051
Heat Shrink Tubing 2:1 Red 19.00MM 5M	15052
Heat Shrink Tubing 2:1 Red 25.40MM 5M	15053
Heat Shrink Tubing 2:1 Red 38.10MM 5M	15054
Heat Shrink Tubing 2:1 Red 50.80MM 5M	15055
Heat Shrink Tubing 2:1 Yellow 1.60MM 100M	13677
Heat Shrink Tubing 2:1 Yellow 2.40MM 100M	13678
Heat Shrink Tubing 2:1 Yellow 3.20MM 100M	13679

Normal Wall Flame Retardant Heat Shrink Tubing

PRO-POWER
Quality Cables

Part Number Table

Description	Part Number
Heat Shrink Tubing 2:1 Yellow 4.80MM 100M	13680
Heat Shrink Tubing 2:1 Yellow 6.40MM 100M	13681
Heat Shrink Tubing 2:1 Yellow 9.50MM 100M	13682
Heat Shrink Tubing 2:1 Yellow 12.7MM 100M	13683
Heat Shrink Tubing 2:1 Yellow 19.0MM 100M	13684
Heat Shrink Tubing 2:1 Yellow 25.4MM 50M	13685
Heat Shrink Tubing 2:1 Yellow 38.1MM 50M	13686
Heat Shrink Tubing 2:1 Yellow 50.8MM 25M	13687
Heat Shrink Tubing 2:1 Yellow 1.60MM 5M	15056
Heat Shrink Tubing 2:1 Yellow 2.40MM 5M	15057
Heat Shrink Tubing 2:1 Yellow 3.20MM 5M	15058
Heat Shrink Tubing 2:1 Yellow 4.80MM 5M	15059
Heat Shrink Tubing 2:1 Yellow 6.40MM 5M	15060
Heat Shrink Tubing 2:1 Yellow 9.50MM 5M	15061
Heat Shrink Tubing 2:1 Yellow 12.70MM 5M	15062
Heat Shrink Tubing 2:1 Yellow 19.00MM 5M	15063
Heat Shrink Tubing 2:1 Yellow 25.40MM 5M	15064
Heat Shrink Tubing 2:1 Yellow 38.10MM 5M	15065
Heat Shrink Tubing 2:1 Yellow 50.80MM 5M	15066
Heat Shrink Tubing 2:1 White 1.60MM 100M	13688
Heat Shrink Tubing 2:1 White 2.40MM 100M	13689
Heat Shrink Tubing 2:1 White 3.20MM 100M	13690
Heat Shrink Tubing 2:1 White 4.80MM 100M	13691
Heat Shrink Tubing 2:1 White 6.40MM 100M	13692
Heat Shrink Tubing 2:1 White 9.50MM 100M	13693
Heat Shrink Tubing 2:1 White 12.70MM 100M	13694
Heat Shrink Tubing 2:1 White 19.00MM 100M	13695
Heat Shrink Tubing 2:1 White 25.40MM 50M	13696
Heat Shrink Tubing 2:1 White 38.10MM 50M	13697
Heat Shrink Tubing 2:1 White 50.80MM 25M	13698
Heat Shrink Tubing 2:1 White 1.60MM 5M	15067
Heat Shrink Tubing 2:1 White 2.40MM 5M	15068
Heat Shrink Tubing 2:1 White 3.20MM 5M	15069
Heat Shrink Tubing 2:1 White 4.80MM 5M	15070
Heat Shrink Tubing 2:1 White 6.40MM 5M	15071

PRO-POWER
Quality Cables

Normal Wall Flame Retardant Heat Shrink Tubing

PRO-POWER
Quality Cables

Part Number Table

Description	Part Number
Heat Shrink Tubing 2:1 White 9.50MM 5M	15072
Heat Shrink Tubing 2:1 White 12.70MM 5M	15073
Heat Shrink Tubing 2:1 White 19.00MM 5M	15074
Heat Shrink Tubing 2:1 White 25.40MM 5M	15075
Heat Shrink Tubing 2:1 White 38.10MM 5M	15076
Heat Shrink Tubing 2:1 White 50.80MM 5M	15077
Heat Shrink Tubing 2:1 Blue 1.60MM 100M	13699
Heat Shrink Tubing 2:1 Blue 2.40MM 100M	13700
Heat Shrink Tubing 2:1 Blue 3.20MM 100M	13701
Heat Shrink Tubing 2:1 Blue 4.80MM 100M	13702
Heat Shrink Tubing 2:1 Blue 6.40MM 100M	13703
Heat Shrink Tubing 2:1 Blue 9.50MM 100M	13704
Heat Shrink Tubing 2:1 Blue 12.7MM 100M	13705
Heat Shrink Tubing 2:1 Blue 19MM 100M	13706
Heat Shrink Tubing 2:1 Blue 25.4MM 50M	13707
Heat Shrink Tubing 2:1 Blue 38.1MM 50M	13708
Heat Shrink Tubing 2:1 Blue 50.8MM 25M	13709
Heat Shrink Tubing 2:1 Blue 1.60MM 5M	15078
Heat Shrink Tubing 2:1 Blue 2.40MM 5M	15079
Heat Shrink Tubing 2:1 Blue 3.20MM 5M	15080
Heat Shrink Tubing 2:1 Blue 4.80MM 5M	15081
Heat Shrink Tubing 2:1 Blue 6.40MM 5M	15082
Heat Shrink Tubing 2:1 Blue 9.50MM 5M	15083
Heat Shrink Tubing 2:1 Blue 12.70MM 5M	15084
Heat Shrink Tubing 2:1 Blue 19.00MM 5M	15085
Heat Shrink Tubing 2:1 Blue 25.40MM 5M	15086
Heat Shrink Tubing 2:1 Blue 38.10MM 5M	15087
Heat Shrink Tubing 2:1 Blue 50.80MM 5M	15088
Heat Shrink Tubing 2:1 Green/Yellow 1.6MM 100M	13710
Heat Shrink Tubing 2:1 Green/Yellow 2.4MM 100M	13711
Heat Shrink Tubing 2:1 Green/Yellow 3.2MM 100M	13712
Heat Shrink Tubing 2:1 Green/Yellow 4.8MM 100M	13713
Heat Shrink Tubing 2:1 Green/Yellow 6.4MM 100M	13714
Heat Shrink Tubing 2:1 Green/Yellow 9.5MM 100M	13715
Heat Shrink Tubing 2:1 Green/Yellow 12.7MM 100M	13716

PRO-POWER
Quality Cables

Normal Wall Flame Retardant Heat Shrink Tubing

Part Number Table

Description	Part Number
Heat Shrink Tubing 2:1 Green/Yellow 19MM 100M	13717
Heat Shrink Tubing 2:1 Green/Yellow 25.4MM 50M	13718
Heat Shrink Tubing 2:1 Green/Yellow 38.1MM 50M	13719
Heat Shrink Tubing 2:1 Green/Yellow 50.8MM 25M	13720
Heat Shrink Tubing 2:1 Green/Yellow 1.60MM 5M	15089
Heat Shrink Tubing 2:1 Green/Yellow 2.40MM 5M	15090
Heat Shrink Tubing 2:1 Green/Yellow 3.20MM 5M	15091
Heat Shrink Tubing 2:1 Green/Yellow 4.80MM 5M	15092
Heat Shrink Tubing 2:1 Green/Yellow 6.40MM 5M	15093
Heat Shrink Tubing 2:1 Green/Yellow 9.50MM 5M	15094
Heat Shrink Tubing 2:1 Green/Yellow 12.70MM 5M	15095
Heat Shrink Tubing 2:1 Green/Yellow 19MM 5M	15096
Heat Shrink Tubing 2:1 Green/Yellow 25.4MM 5M	15097
Heat Shrink Tubing 2:1 Green/Yellow 38.1MM 5M	15098
Heat Shrink Tubing 2:1 Green/Yellow 50.8MM 5M	15099
Heat Shrink Tubing 2:1 Brown 1.6MM 100M	13721
Heat Shrink Tubing 2:1 Brown 2.4MM 100M	13722
Heat Shrink Tubing 2:1 Brown 3.2MM 100M	13723
Heat Shrink Tubing 2:1 Brown 4.8MM 100M	13724
Heat Shrink Tubing 2:1 Brown 6.4MM 100M	13725
Heat Shrink Tubing 2:1 Brown 9.5MM 100M	13726
Heat Shrink Tubing 2:1 Brown 12.7MM 100M	13727
Heat Shrink Tubing 2:1 Brown 19MM 100M	13728
Heat Shrink Tubing 2:1 Brown 25.4MM 50M	13729
Heat Shrink Tubing 2:1 Brown 38.1MM 50M	13730
Heat Shrink Tubing 2:1 Brown 50.8MM 25M	13731
Heat Shrink Tubing 2:1 Brown 1.60MM 5M	15100
Heat Shrink Tubing 2:1 Brown 2.40MM 5M	15101
Heat Shrink Tubing 2:1 Brown 3.20MM 5M	15102
Heat Shrink Tubing 2:1 Brown 4.80MM 5M	15103
Heat Shrink Tubing 2:1 Brown 6.40MM 5M	15104
Heat Shrink Tubing 2:1 Brown 9.50MM 5M	15105
Heat Shrink Tubing 2:1 Brown 12.7MM 5M	15106
Heat Shrink Tubing 2:1 Brown 19MM 5M	15107

Normal Wall Flame Retardant Heat Shrink Tubing

Part Number Table

Description	Part Number
Heat Shrink Tubing 2:1 Brown 25.4MM 5M	15108
Heat Shrink Tubing 2:1 Brown 38.1MM 5M	15109
Heat Shrink Tubing 2:1 Brown 50.8MM 5M	15110

Normal Wall Flame Retardant Heat Shrink Tubing

PRO-POWER
Quality Cables

Notes:

International Sales Offices:



AUSTRALIA – Farnell InOne
Tel No: ++ 61 2 9645 8888
Fax No: ++ 61 2 9644 7898



FINLAND – Farnell InOne
Tel No: ++ 358 9 560 7780
Fax No: ++ 358 9 345 5411



NETHERLANDS – Farnell InOne
Tel No: ++ 31 30 241 7373
Fax No: ++ 31 30 241 7333



SWITZERLAND – Farnell InOne
Tel No: ++ 41 1 204 64 64
Fax No: ++ 41 1 204 64 54



AUSTRIA – Farnell InOne
Tel No: ++ 43 662 2180 680
Fax No: ++ 43 662 2180 670



FRANCE – Farnell InOne
Tel No: ++ 33 474 68 99 99
Fax No: ++ 33 474 68 99 90



NEW ZEALAND – Farnell InOne
Tel No: ++ 64 9 357 0646
Fax No: ++ 64 9 357 0656



UK – Farnell InOne
Tel No: ++ 44 8701 200 200
Fax No: ++ 44 8701 200 201



BELGIUM – Farnell InOne
Tel No: ++ 32 3 475 2810
Fax No: ++ 32 3 227 3648



GERMANY – Farnell InOne
Tel No: ++ 49 89 61 39 39 39
Fax No: ++ 49 89 613 59 01



NORWAY – Farnell InOne
Tel No: ++ 45 44 53 66 66
Fax No: ++ 45 44 53 66 02



UK – BuckHickman InOne
++ 44 8450 510 150
++ 44 8450 510 130



BRAZIL – Farnell-Newark InOne
Tel No: ++ 55 11 4066 9400
Fax No: ++ 55 11 4066 9410



HONG KONG – Farnell-Newark InOne
Tel No: ++ 852 2268 9888
Fax No: ++ 852 2268 9899



PORTUGAL – Farnell InOne
Tel No: ++ 34 93 475 8804
Fax No: ++ 34 93 474 5288



UK – CPC
++ 44 8701 202 530
++ 44 8701 202 531



CHINA – Farnell-Newark InOne
Tel No: ++86 10 6238 5152
Fax No: ++86 10 6238 5022



IRELAND – Farnell InOne
Tel No: ++ 353 1 830 9277
Fax No: ++ 353 1 830 9016



SINGAPORE – Farnell-Newark InOne
Tel No: ++ 65 6788 0200
Fax No: ++ 65 6788 0300



EXPORT – Farnell InOne
Tel No: ++ 44 8701 200 208
Fax No: ++ 44 8701 200 209

For enquiries from all other markets



DENMARK – Farnell InOne
Tel No: ++ 45 44 53 66 44
Fax No: ++ 45 44 53 66 06



ITALY – Farnell InOne
Tel No: ++ 39 02 93 995 200
Fax No: ++ 39 02 93 995 300



SPAIN – Farnell InOne
Tel No: ++ 34 93 475 8805
Fax No: ++ 34 93 474 5107



ESTONIA – Farnell InOne
Tel No: ++ 358 9 560 7780
Fax No: ++ 358 9 345 5411



MALAYSIA – Farnell-Newark InOne
Tel No: ++ 60 3 7873 8000
Fax No: ++ 60 3 7873 7000



SWEDEN – Farnell InOne
Tel No: ++ 46 8 730 50 00
Fax No: ++ 46 8 83 52 62

<http://www.farnellinone.com>

<http://www.buckhickmaninone.com>

<http://www.cpc.co.uk>

Disclaimer This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Pro-Power is the registered trademark of the Group. © Premier Farnell plc 2004.

PRO-POWER
Quality Cables