

datasheet for KLEPS 2900
 article number: 972309100



product description:	order number: 972 309-100
description:	Safety clamp-type test probe with rigid hook to ensure secure clamping of eyes, pins, wires and boards. 4 mm brass socket connection. Connects with safety measuring leads.
typ:	KLEPS 2900 schwarz/black
system:	4 mm safety system
order number:	972 309-100
clamping range:	5.5 mm
clamping typ:	hook
color	●
other color versions:	● ●
technical data	
measurement category	CAT III
norm	DIN EN 61010-031
type of termination:	4 mm socket
rated voltage:	AC/DC 1000 V
rated current:	20 A
contact resistance:	50 mOhm
material	
contact material:	stainless steel
contact surface material:	nickel-plated
housing material:	PBT
environmental conditions:	
temperature range:	-25 °C to +80 °C
inflammable class:	
housing:	94 HB
drawing	