



datasheet for PRUEF 2600 C2
 article number: 972327100



product description:	order number: 972 327-100
description:	Test probe shatter - proof insulating sleeve and slender stainless steel tip. Tip for penetration of insulation and oxide layers. 4mm diameter brass socket connection. Connection with safety measuring leads. component part: protector and IC - tap SS 260
typ:	PRUEF 2600 C2 schwarz / black
system:	4mm safety system
order number:	972 327-100
color	
other color versions:	
technical data	
measurement category	CAT II
norm	DIN EN 61010-031
pin dimensions	2mm
type of contact:	to touch
type of termination:	4mm socket, unsprung
rated voltage:	AC-DC 1000V
rated current:	1A
contact resistance:	50mOhm
material	
contact material:	stainless steel
contact surface material:	nickel
housing material:	PP
environmental conditions:	
temperature range:	-25°C to +80°C
inflammable class:	
housing:	94 HB
drawing	

