



datasheet for BIL 30  
article number: 930166103



<b>product description:</b>	order number: 930 166-103
<b>description:</b>	Socket with insulated head and ring for installation in equipment chassis and switchpanels up to 4 mm wall thickness. 4 mm diameter tin-plated brass socket, with solder connection.
<b>typ:</b>	BIL 30 gelb/yellow
<b>system:</b>	4 mm system
<b>order number:</b>	930 166-103
<b>color</b>	
<b>other color versions:</b>	
<b>technical data</b>	
<b>type of contact:</b>	unsprung socket
<b>type of termination:</b>	solder
<b>rated voltage:</b>	DC 60 V
<b>rated current:</b> <a href="#">Please consider derating curve!</a>	32 A
<b>contact resistance:</b>	5 mOhm
<b>mounting:</b>	screw
<b>material</b>	
<b>contact material:</b>	brass
<b>contact surface material:</b>	tin-plated
<b>connecting nut material:</b>	brass nickel-plated
<b>environmental conditions:</b>	
<b>temperature range:</b>	-25 °C to +85 °C
<b>drawing</b>	
	