

datasheet for PKNI 10 B
 article number: 930136100



product description:	order number: 930 136-100
description:	Pole terminal with claw edge, captive insulated head and insulated ring. 6 mm diameter nickel-plated brass threaded bolt with 2.6 mm diameter transverse hole. For insulated non-rotating installation in equipment chassis and switch panels up to 3.5 mm wall
typ:	PKNI 10 B schwarz/black
system:	4 mm system
order number:	930 136-100
color	●
other color versions:	● ●
technical data	
type of contact:	spring unloaded socket
type of termination:	M 6 thread
rated voltage:	DC 60 V
rated current:	63 A
contact resistance:	2 mOhm
mounting:	screw
material	
contact material:	brass
contact surface material:	nickel-plated
housing material:	PF
environmental conditions:	
temperature range:	-25 °C to +100 °C
inflammable class:	
housing:	94 V-0
drawing	
<p>The drawing shows two views of the pole terminal. The left view is a perspective view of the housing with dimensions 9 (width), 9.9 (depth), and a 90-degree angle. The right view is a side view showing the internal components and mounting details. Dimensions include: 17 (total height), 2.6 (transverse hole diameter), 52 (total length), 20 (length to the end of the housing), 0.8 (thread pitch), and M6x0.75 (thread specification). The label 'Einbauöffnung' points to the mounting hole.</p>	