



datasheet for MA 1 Crimp
 article number: 930318101



product description:	order number: 930 318-101
description:	Miniature alligator clip with high strength insulation and nickel-plated brass / bronze jaws. The flat part of the chuck jaws (fine wire section) allows a secure con-tacting, when thin wires be pinched. It is possible to clamp of flat components (soldering eyes) and wires up to a maximum diameter of 4mm. Crimp connection for 0,25mm ² up to 0,5mm ² wiring, with following assembly of the bottom insulating part (shim). With suitable tool to crimp (for example with Tyco use 539680 - 2).
typ:	MA 1 Crimp rot/red
order number:	930 318-101
clamping range:	conductor with max. Ø 4 mm
color	
other color versions:	
technical data	
type of contact:	to clamp
type of termination:	Crimp 0,25 mm ² up to 0,5 mm ²
rated voltage:	DC 60 V
contact resistance:	5 mOhm
material	
contact material:	brass / bronze
contact surface material:	nickel
housing material:	PA
environmental conditions:	
temperature range:	-25°C up to +100°C
inflammable class:	
housing:	94 HB
drawing	