



datasheet for MA 260 SH
 article number: 973889101



product description:	order number: 973 889-101
description:	Contact-protected Miniature alligator clip with high strength insulation and nickel-plated bronze jaws. Clamping range up to a bolt diameter of 6 mm. The part of the jaws (fine wire section) allows a secure contact to be made when clamping even the thinner wire. 4 mm diameter brass socket connection.
typ:	MA 260 SH rot/red
system:	4 mm safety system
order number:	973 889-101
clamping range:	conductor with maximum Ø 6mm
color	
other color versions:	
technical data	
measurement category	CAT II
norm	DIN EN 61010-031
type of contact:	to clamp
type of termination:	4 mm socket
rated voltage:	AC/DC 300 V
rated current:	15 A
contact resistance:	5mOhm
material	
contact material:	bronze
contact surface material:	nickel
housing material:	PA
environmental conditions:	
temperature range:	from -25 °C to +80 °C
inflammable class:	
housing:	94 HB
drawing	
	