

## 1-1838225-0 Product Details


**Have a Question?**

Chat with a Product Information Specialist



### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)



**1-1838225-0**

TE Internal Number: 1-1838225-0

**Active**

### Quick Disconnect Tabs, Tab Adapters & Tab Caps

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

#### Product Highlights:

- Terminal
- Terminal Type = Tab
- Tab Type = Wire Crimp
- Insulated
- Mating Area Interface Dimensions = 6.35 x 0.80 mm

[View all Features](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

### Documentation & Additional Information

#### Product Drawings:

- [EURO-CRIMP INSULATED RED MALE PUSH-ON TERMINAL 0.5mm...](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- [Euro-Crimp Terminals and Splices](#) (PDF, English)

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- [Product Type](#) = Terminal
- Terminal Type = Tab
- [Insulation](#) = Yes
- [Mating Area Interface Dimensions \(mm \[in\]\)](#) = 6.35 x 0.80 [.250 x .031]
- [Material](#) = Brass
- [Insulation Diameter \(mm \[in\]\)](#) = 3.56 [.140] Max.
- [Finish](#) = None
- [Wire/Cable Type](#) = Regular Wire
- [Mount Angle](#) = Straight
- Insulation Support = Without
- Color = Red
- Proprietary Name = EURO-CRIMP

#### Electrical Characteristics:

- [Dimple](#) = With

#### Body Related Features:

- [Tab Type](#) = Wire Crimp
- [Wire Range \(mm \[AWG\]\)](#) = 0.30-1.40<sup>2</sup> [22-16]
- Stud Hole = Without
- Insulation Sleeve Material = PVC

#### Housing Related Features:

- UL Flammability Rating = UL 94V-0

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

#### Packaging Related Features:

- [Packaging Method](#) = Loose Piece

#### Other:

- Brand = AMP

BOOKMARK

### Corporate Information

- [Who We Are](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)

### Quick Links

- [Check Distributor Inventory](#)
- [Cross Reference](#)
- [Find Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

### Customer Support

- [Email or Chat with Us](#)
- [Find a Phone Number](#)
- [Search Knowledge Base](#)
- [Manage Your Account](#)

### Sign up for our eNewsletter

Enter your email address

### Follow Us On:



### Visit Us On:

