

## 1-1838230-0 Product Details


### Have a Question?

Chat with a Product Information Specialist



### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)



**1-1838230-0**

TE Internal Number: 1-1838230-0

Active

### Quick Disconnect Receptacles - Insulated

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

#### Product Highlights:

- Proprietary Name = EURO-CRIMP
- Receptacle Style = Receptacle/Tab Combination
- Wire Range = 3.00-6.00<sup>2</sup> [12-10] mm [AWG]
- Mating Area Interface Dimensions = 6.35 x 0.80 mm
- Insulation Diameter = 6.35 [.250] Max. mm [in]

[View all Features](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

### Documentation & Additional Information

#### Product Drawings:

- [EURO-CRIMP INSULATED YELLOW PIGGY BACK TERMINAL 4.0m...](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- [Euro-Crimp Terminals and Splices](#) (PDF, English)

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- [Proprietary Name](#) = EURO-CRIMP
- [Receptacle Style](#) = Receptacle/Tab Combination
- [Mating Area Interface Dimensions \(mm \[in\]\)](#) = 6.35 x 0.80 [.250 x .031]
- [Insulation Diameter \(mm \[in\]\)](#) = 6.35 [.250] Max.
- [Insertion Force](#) = Normal
- [Material](#) = Brass
- [Finish](#) = None
- [Dimple Type](#) = Dimple without wire stop
- [Insulation Support](#) = Insulation Support
- [Color](#) = Yellow

#### Electrical Characteristics:

- [Voltage \(VAC\)](#) = 600

#### Body Related Features:

- [Fully Insulated](#) = No
- [Wire Range \(mm \[AWG\]\)](#) = 3.00-6.00<sup>2</sup> [12-10]
- [Insulation Sleeve Material](#) = PVC
- [Stock Thickness \(mm \[in\]\)](#) = 0.41 [0.016]

#### Housing Related Features:

- [UL Flammability Rating](#) = UL 94V-0

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- [RoHS/ELV Compliance History](#) = Always was RoHS compliant

#### Packaging Related Features:

- [Packaging Method](#) = Loose Piece

#### Other:

- [Brand](#) = AMP

BOOKMARK

### Corporate Information

- [Who We Are](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)

### Quick Links

- [Check Distributor Inventory](#)
- [Cross Reference](#)
- [Find Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

### Customer Support

- [Email or Chat with Us](#)
- [Find a Phone Number](#)
- [Search Knowledge Base](#)
- [Manage Your Account](#)

### Sign up for our eNewsletter

Enter your email address

### Follow Us On:



### Visit Us On:

