



**NEW**  
Magnifying  
Lamp

**108**  
Bright  
White LEDs



**High-Intensity Illumination**  
**Extra Large Lens**  
**5 Diopter Spot Lens**

# ProVue Touch LED Magnifying Lamp

## Extra enlargement capability

The ProVue Touch with shadow free illumination and 5 diopter spot lens is suited for engineering, fabrication, laboratory and quality control applications. A touch-sensitive switch allows three-stage intensity control of the magnifying lamp. A spring-balanced arm extends 35 inches and remains fixed in any position for hands-free magnification.

## Specifications

PROVUE TOUCH LED MAGNIFYING LAMP	
<b>MAGNIFICATION</b>	1.75X (3-Diopter)   2.25x (5-Diopter) Spot Lens
<b>LENS DIAMETER</b>	7in
<b>ADJUSTABLE ARM LENGTH</b>	35in
<b>COLOR</b>	White
<b>BULB</b>	108 LEDs

Order #	Description
<b>26508-LED</b>	<b>ProVue Touch LED Magnifying Lamp - White</b>

## Features:

- Modern slim design
- Large 7" Crystal Clear 1.75x (3 diopter) lens
- 2.25x – 5 diopter power spot lens mounted
- ABS plastic housing
- Lens can be easily removed and replaced when necessary
- Lens cover included for protection
- 35" industrial grade spring balanced enclosed arm. Stays put in any position
- Built in metal grips for quick and easy positioning
- Heavy duty metal clamp with a 3-1/2" opening
- Dual voltage: Operates at 110v or 220v
- 108 energy saving white LEDs provides shadow free illumination. (Lumen: 420LM) (Color Temperature: 6400K)
- Touch Sensitive 3 stage on-off switch & for controlling light intensity



**NEW**  
Magnifying  
Lamp

**72**  
UV LED  
Lights

**108**  
Bright  
White LEDs



**High-Intensity Illumination**  
**Extra Large Lens**  
**Dual LED Operation**

# ProVue Touch Dual LED Magnifying Lamp

## Provides Shadow Free Illumination

The ProVue Touch Dual with UV lighting extends the functionality for forensic analysis, such as detecting fraudulent identification and currency, analyzing minerals, inspection in the biological fields and other tasks requiring high contrast in bright settings. The ProVue Touch Dual can quickly switch between UV and White LEDs with two separate touch-sensitive switches.

## Specifications

PROVUE TOUCH DUAL LED MAGNIFYING LAMP	
<b>MAGNIFICATION</b>	1.75X (3-Diopter)   2.25x (5-Diopter) Spot Lens
<b>LENS DIAMETER</b>	7in
<b>ADJUSTABLE ARM LENGTH</b>	35in
<b>COLOR</b>	White
<b>BULB</b>	108 White LEDs   72 UV LEDs
Order #	Description
<b>26508-LDV</b>	<b>ProVue Touch Dual LED Magnifying Lamp - White</b>

## Features:

- Modern slim design
- Large 7" Crystal Clear 1.75x (3 diopter) lens
- 2.25x – 5 diopter power spot lens mounted
- ABS plastic housing
- Lens can be easily removed and replaced when necessary
- Lens cover included for protection
- 35" industrial grade spring balanced enclosed arm stays put in any position
- Built in metal grips for quick and easy positioning
- Heavy duty metal clamp with a 3-1/2" opening
- Dual voltage: Operates at 110v or 220v
- 180 energy saving LEDs provides shadow free illumination. (72 UV LEDs operating at 395-400NM). (UV: 102LM | LED Light 420LM) (Color Temperature 6400K)
- Two Touch Sensitive 3 stage on-off switch & for controlling white or UV light intensity