


PCB TERMINAL BLOCKS

3.5mm Pitch Ultra Low Profile Commercial Screw Terminal

- Ultra low profile
- Stainless steel wire protector
- 2-12 pole interlocking
- 4-12 pole pre-assembled
- UL94-V0 flame retardant PA
- Double interlock mechanism for increased strength
- 1mm² cable entry
- Anti solder wicking terminals
- Captive screws
- Guided pin alignment
- Standard colour black. Other colours available
-  us approved


CTB3051



SPECIFICATION

Rating	6A/300V
Dielectric strength	1.5kV
Working temperature	105°C
Moulding	UL94-V0 flame retardant PA
Pin/terminal	Tinned, nickel plated copper flash brass
Screw/torque	M2 steel zinc plated, 0.4Nm max
Recommended PCB hole size	ø1.2mm

TYPE NO.	POLES	LENGTH
CTB3051/2BK	2	7mm
CTB3051//BK	3	10.5mm
CTB3051/4BK	4	14mm
CTB3051/5BK	5	17.5mm
CTB3051/6BK	6	21mm
CTB3051/7BK	7	24.5mm
CTB3051/8BK	8	28mm
CTB3051/9BK	9	31.5mm
CTB3051/10BK	10	35mm
CTB3051/11BK	11	38.5mm
CTB3051/12BK	12	42mm



PCB
TERMINAL
BLOCKS

INTER-
CONNECTION

FUSES &
FUSE-
HOLDERS

LEDs &
INDICATORS

MINIATURE
SWITCHES

LIMIT &
SAFETY
SWITCHES

CONTROL
PRODUCTS

INTERFACE
MODULES &
SUPPORTS

RELAY
BASES

ENCLOSURES

BATTERIES

TRANS-
FORMERS