

PCB TERMINAL BLOCKS

5mm Pitch Commercial Standard Profile Screw Terminal

PCB
TERMINAL
BLOCKS

INTER-
CONNECTION

FUSES &
FUSE-
HOLDERS

LEDs &
INDICATORS

MINIATURE
SWITCHES

LIMIT &
SAFETY
SWITCHES

CONTROL
PRODUCTS




INTERFACE
MODULES &
SUPPORTS

RELAY
BASES

ENCLOSURES

BATTERIES

TRANS-
FORMERS

- 2-12 pole solid block
- End stackable
- Moulded in grey UL94-V0 flame retardant PC
- Wire protector terminals
- 0.5-4.0mm² (30-12AWG) solid cable
- 0.5-2.5mm² (30-12AWG) stranded cable
- Captive screw
- Anti solder wicking terminal
- Guided pin alignment
- 13 & 14 pole available on request
-   , approved

CTB1500



TYPE NO.	POLES	LENGTH
CTB1500/2	2	10mm
CTB1500/3	3	15mm
CTB1500/4	4	20mm
CTB1500/5	5	25mm
CTB1500/6	6	30mm
CTB1500/7	7	35mm
CTB1500/8	8	40mm
CTB1500/9	9	45mm
CTB1500/10	10	50mm
CTB1500/11	11	55mm
CTB1500/12	12	60mm

SPECIFICATION

Rating	24A/250V
	UL=18A/300V, VDE&IMQ=24A/250V
Dielectric strength	≥2kV
Impulse withstand voltage	4kV
Working temperature	85°C
Moulding	UL94-V0 flame retardant PC
Pin/terminal	Tinned, nickel plated brass
Wire protector	Nickel plated brass
Screw/torque	M2.5 steel zinc plated, 0.5Nm
Recommended PCB hole size	ø1.1mm

