



FUSES & FUSEHOLDERS

8.5x31.5mm & 10.3x38mm aR Semiconductor Power Fuses

- Fast aR type for semiconductor protection
- Current limiting, super fast blow
- To IEC 60269
- CF08aR 400V rating
- CF10aR 500V standard rating, 690V and 1000V available
-  250mA-32A all voltage
-  250mA-32A 500V



SPECIFICATION

Rating	CF08aR	400V	500mA - 25A
	CF10aR	500V	250mA - 15A
Breaking capacity	CF08aR	20kA	
	CF10aR	120kA	
Blow time @ $I_N = 1A$		min 4 hours	
Blow time @ $I_N = 4A$	250mA - 5A	3ms - 1s	
	6A - 32A	10ms - 10	
Blow time @ $I_N = 10A$	250mA - 5A	max 20ms	
	6A - 32A	max 30ms	

8.5x31.5mm 400V

TYPE NO.	RATING
CF0840aR/500	500mA
CF0840aR/630	630mA
CF0840aR/800	800mA
CF0840aR/1	1A
CF0840aR/1.25	1.25A
CF0840aR/2	2A
CF0840aR/2.5	2.5A
CF0840aR/3	3A
CF0840aR/3.5	3.5A
CF0840aR/4	4A
CF0840aR/5	5A
CF0840aR/6	6A
CF0840aR/6.3	6.3A
CF0840aR/7	7A
CF0840aR/8	8A
CF0840aR/9	9A
CF0840aR/10	10A
CF0840aR/12	12A
CF0840aR/12.5	12.5A
CF0840aR/15	15A
CF0840aR/16	16A
CF0840aR/20	20A
CF0840aR/25	25A

10.3x38mm 500V

TYPE NO.	RATING
CF1050aR/250	250mA
CF1050aR/315	315mA
CF1050aR/400	400mA
CF1050aR/500	500mA
CF1050aR/630	630mA
CF1050aR/800	800mA
CF1050aR/1	1A
CF1050aR/1.25	1.25A
CF1050aR/1.6	1.6A
CF1050aR/2	2A
CF1050aR/2.5	2.5A
CF1050aR/3	3A
CF1050aR/3.15	3.15A
CF1050aR/4	4A
CF1050aR/5	5A
CF1050aR/6	6A
CF1050aR/6.3	6.3A
CF1050aR/7	7A
CF1050aR/8	8A
CF1050aR/9	9A
CF1050aR/10	10A
CF1050aR/12	12A
CF1050aR/12.5	12.5A
CF1050aR/15	15A

