

H0,5/10**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16


D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-2083

www.weidmueller.com



- For conductors from 0.25 to 6,0 mm² (AWG 24 - 10)
tin-plated copper
dimensional tolerances to DIN 46228 part 1
- supplied loose in polybag

General ordering data

Order No.	9004050000
Type	H0,5/10
Version	Wire end ferrule, 0.5 mm ²
GTIN (EAN)	4008190153052

H0,5/10**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-2083

www.weidmueller.com

Technical data**Dimensions**

Length	10 mm
--------	-------

Product data

Conductor cross-section	0.5 mm ²	Contact surface diameter (D1)	1 mm
Collar diameter (D2)	2.1 mm		

Classifications

ETIM 2.0	EC000005	ETIM 3.0	EC000005
UNSPSC	31-16-31-02	eClass 4.1	27-06-07-01
eClass 5.1	27-40-02-01	eClass 6.0	27-40-02-01
eClass 7.0	27-40-02-01		

Product information

Description of article	Wire end ferrule without plastic collar
------------------------	-----------------------------------------