



[3M ESPE Dental Professionals](#) > [Products](#) > [Product Catalog](#)

[Tapes](#) > [3M™ Tartan™ General Use Vinyl Electrical Insulating Tape 1710, 3/4 in x 60 ft](#)

3M™ Tartan™ General Use Vinyl Electrical Insulating Tape 1710, 3/4 in x 60

UPC# 00054007496564 3M Product Number 1710-3/4"X60'-1-1/2"CORE 3M Product Number 1710-3/4"X60FT
3M Product Number 49656 3M ID 80611433329

Included **1**
Body ID:
12736725



On a 1 1/2 inch core, this black, 7 mil vinyl tape is a good quality, economical general insulating tape. Its elastic backing ensures easy, moisture-tight conformation to irregular surfaces.

Overview | [Support](#)

3M™ Tartan™ General Use Vinyl Electrical Insulating Tape 1710 offers good resistance to abrasion, moisture, alkalis, acid, copper corrosion, and varying weather conditions (including ultraviolet). UL Listed and is flame-retardant.

Specifications

Backing Material	Polyvinyl Chloride
China RoHS - Below MCV	Yes
Color	Black
EU RoHS Compliant	Yes
Length	60 Linear Foot
Maximum Operating Temperature (Celsius)	80 Degree Celsius
Product Type	Vinyl Tape
Tape Length	60 Linear Yard
Tape Length (metric)	2 m
Tape Width	0.75 in
Tape Width (metric)	1.9 cm
Thickness	7 Milli-inch (mil)
Width	3/4 Inch

Support | [Overview](#)

Info

[3M\(TM\) Electrical OEM Tapes UL Matrix](#) (PDF, 11.9KB)

MSDS

[3M\(TM\) Temflex\(TM\) General Use Vinyl Electrical Tapes 1700P \(and 1700C \(Colors\)\); 3M\(TM\) Tartan\(TM\) General Use Vinyl Electrical Insulating Tape 1710 \(US\)](#)