



Where To Buy

Enter Zip Code:

Enter Quantity:

GO

Sta-Kon®

PRINT

Ring Terminal

T&B Catalog Number: BC14-10
UPC Number: 78621080129
Status: Active

Description:
 Non-Insulated Ring Terminal For Wire Range heavy duty 16-14 Stud Size #10, Mt

ROHS SUBMITTAL PACKAGE

Features

- These non-insulated ring terminals are made of electrolytic copper for high cor installed with crimping tools having a single indentor or double indentor (recon Serrated barrel increases grip on wire.

General

Insulation Type	Non-Insulated
Terminal Series	BC
Material	Copper
Finish	Electro -Tin Plated
Color	Metallic
Wire Range	heavy duty 16-14
Stud Size	#10

Dimension Information

Stock Thickness	.05
A (inches)	.87
B (inches)	.39
C (inches)	.29
M (inches)	.68

Specifications

Temperature Rating	150°C
Voltage Rating	600V
Flammability Rating	UL 94 V-0

Tooling

[Tool Charts](#)
[Application Tools](#)
[Recommended Tool](#)

[Click Here](#)
[WT110M, WT111M, WT112](#)
[ERG4002, ERG4005](#)

Packaging

Order Multiple	50
Inner Package	50
Outer Package	250
Package Type	Standard
Package Height	3.3
Package Length	4.6
Package Width	3.3
T&B Sold in UOM	Each
T&B Weight Per UOM	0.56 lbs. per 100
Alternate Package Qty	BC87

Application Support

[Overview](#)
[Wire Guide Tables](#)

[Click Here](#)
[Click Here](#)