



Where To Buy

Enter Zip Code:

Enter Quantity:

GO

Sta-Kon®

PRINT

Ring Terminal

T&B Catalog Number: RZ22-2
UPC Number: 78621080452
Status: Active

Description:
 Insulated Nylon Ring Terminal For Wire Range 26-22 Stud Size #2, Yellow

ROHS SUBMITTAL PACKAGE

Features

- Self-insulated with high dielectric-strength nylon sleeves. An inner bronze insula the flexing radius of the conductor and eliminates conductor creep.

General

Insulation Type	Insulated Nylon
Terminal Series	RZ
Material	Copper
Finish	Electro -Tin Plated
Color	Yellow
Wire Range	26-22
Stud Size	#2

Dimension Information

Maximum Insulation (inches)	.083
Stock Thickness	.02
A (inches)	.57
B (inches)	.14
C (inches)	.13
M (inches)	.49

Specifications

Temperature Rating	105°C
Voltage Rating	600V
Flammability Rating	UL 94 V-2

Tooling

Tool Charts [Click Here](#)

Application Tools [WT1452](#)
 Recommended Tool [ERG4006](#)

Packaging

Order Multiple	100
Inner Package	100
Outer Package	500
Package Type	Standard
Package Height	2.6
Package Length	4.8
Package Width	1.8
T&B Sold in UOM	Each
T&B Weight Per UOM	0.15 lbs. per 100

Application Support

T&B Sales Drawings [wsd-000204](#)

Overview [Click Here](#)